

## Features

- Plastic jaw covers to prevent damage to workpiece.
- Locking thumb screw to clamp jaws closed.
- Jaws move in parallel throughout use.
- Long-lasting return spring.
- Zinc-plated handles with detailing for added grip.

## RS PRO Clamping Parallel Plier With Plastic Jaw Inserts 160 mm

RS Stock No.: 0606312



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

## RS PRO Clamping Parallel Plier With Plastic Jaw Inserts

The must-have tool for detailed working. designed with plastic jaws for flawless, damage-free finish.

Engineered with plastic-covered parallel jaws. Grip firmly without damage to delicate pieces. Spring return for easy handling of parts.

Locking screw holds workpiece in place, leaving your hands free.

### Benefits

- Hold a delicate workpiece without fear of damage.
- Hands-free working as jaws can be locked firmly closed.
- Parallel jaws grip securely along their whole length.
- Easier handling of parts due to return spring.
- Built to last, with a robust construction and rust-resistant finish.

### Applications

An essential tool for holding, clamping and bending small workpieces including soft malleable materials. Ideal for:

- Design engineers.
- Maintenance technicians.
- Model builders.

## General Specifications

Plier Type	Clamping Plier with Plastic Jaw Inserts
Number of Pieces	1
Overall Length	168 mm
Cutting Capacity	N/A
Material	Steel jaws with plastic inserts, zinc-plated steel handles
ESD Safe	No
Jaw Opening	13 mm
Jaw Width	12.5 mm
Jaw Length	20 mm usable jaw length
Non Sparking	No
Height Safe	No

## Approvals

Declarations	REACH DoC
--------------	-----------

## Similar Products

Stock No.	Brand	Product Name	Jaw Opening	Parallel	Overall Length
0606317	RS PRO	CENTRE CONDUCTOR CUTTING NIPPER	Up to 25 mm (Duct Rod Ø)	No	110 mm
0606320	RS PRO	Bullet & Snap Connector Insert Tool	46mm	No	145mm
0606319	RS PRO	Spanner Quick Grip	25 mm Max	No	135mm
0606316	RS PRO	Security Crimping and Cutter Plier	0.9mm (Ø cables)	No	212mm
0434623	RS PRO	Snipe Nose Serrated Jaws Parallel Plier	10mm	Yes	125mm
0606318	RS PRO	Snipe Nose Smooth Jaws Parallel Plier	10mm	Yes	125mm
0434621	RS PRO	Fine Nose Round Jaws Parallel Plier	11mm	Yes	125mm
0606312	RS PRO	Fine Clamping Plastic Jaws Parallel Plier	20mm	Yes	168mm
0434622	RS PRO	Flat Nose Nylon Jaws Parallel Plier	10mm	Yes	140mm
0441178	RS PRO	Side Cutter Parallel Plier for Hard Wire 125mm	10mm	Yes	125mm
0606314	RS PRO	Side Cutter Parallel Plier for Hard Wire 160mm	14mm	Yes	167mm
0606313	RS PRO	Side Cutter Parallel Plier for Hard Wire 140mm	8mm	Yes	140mm
0434617	RS PRO	Side Cutter Parallel Plier for Hard Wire 140mm, w/ Grip Handle	8mm	Yes	140mm

