

"PanelSeT SF/SM partial 19" swing rack - 601 mm"

Local distributor code: 398252450

NSYRSWP12

EAN Code: 3606480067341

Main

Range	PanelSeT	
Accessory / separate part category	Mounting accessory	
Product or component type	19" rack	
Application	Electronic application	
For enclosure nominal dimensions	- H: 601 mm	
Rack type	Swing	
Mounting location	Front of enclosure	
Mounting support	Partial 19" swing rack support	
Range compatibility	PanelSeT PanelSeT SF PanelSeT PanelSeT SM	
Device composition	1 rack	
Number of units 19"	12	

Complementary

Rack coverage	Partial	
Material	Steel	
Enclosure/cubicle description	Floor-standing enclosure	
Surface finish	Zinc coated	
Lock type	Lock 5 mm double bar	
fixing mode	By fixing element	
Adjustment	Adjustable in depth every 25 mm	
Permanent permissible load	2 kg per unit	
Opening of the 19" racks	Reversible 120 °	
Height	601 mm	
Width	600 mm 800 mm	
Depth	601 mm	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.500 cm

Package 1 Width	51.500 cm
Package 1 Length	61.500 cm
Package 1 Weight	3.440 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	20
Package 2 Height	105.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	82.000 kg

Logistical informations

Country of origin ES

Contractual warranty

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	24
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions




Image of product / Alternate images

Alternative

