

Specifications



Eaton 36TDQSJ16

Eaton Bussmann series medium voltage DIN fuse, 16 A, AC 36 kV, 2", 51 x 537 mm, backup, DIN, with striker

General specifications

PRODUCT NAME	Eaton Bussmann series medium voltage DIN fuse
CATALOG NUMBER	36TDQSJ16
MODEL CODE	36KV 16A 2" DIN Resin Seal Fuse
UPC	051712186421
EAN	5027590045759
PRODUCT LENGTH/DEPTH	537 mm
PRODUCT HEIGHT	54 mm
PRODUCT WIDTH	51 mm
PRODUCT WEIGHT	2900 g
WARRANTY	Not Applicable
COMPLIANCES	DIN 43625 VDE 0670-4 IEC 60282-1
CERTIFICATIONS	UL VDE
GLOBAL CATALOG	36TDQSJ16
PRODUCT TYPE	Medium voltage DIN fuse



Powering Business Worldwide

Product specifications

USED WITH	270303 Fuse clip A3354710 Fuse clip
AMPERAGE RATING	16 A
FUSE INDICATOR	With Striker
FUSE SIZE	51 x 537 mm
BREAKING CAPACITY	35.5 kA
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Primary side transformer protection
RATED FREQUENCY - MAX	50 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	Other
STANDARD	DIN
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	Yes
CLASS	Class back-up
BARRELS	1
CONSTRUCTION TYPE	Bolt-on
PRE ARC (I2T)	4.6 x 100
RESISTANCE	165 Ohms
WATT LOSSES	52 W
FUSE DIAMETER	51 mm
COLOR	Brown
INTERRUPT RATING	35.5 kAIC
CONSTRUCTION SIZE	51 x 537 mm
MOUNTING METHOD	Clip-in
PACKAGING TYPE	Standard
QUANTITY	1
VOLTAGE RATING	36 kV
TYPE	Fuse
SPECIAL FEATURES	Back-up, Transformer protection, Indoor or outdoor use
APPLICATION	<ul style="list-style-type: none">• transformer protection• indoor or outdoor

Resources

	36TDQSI16~36KV 16Amp 2 DIN Resin Seal Fuse
CATALOGS	Bussmann series complete full line catalog no. 1007
	720107 36kV DIN medium voltage fuses
	720104 12kV DIN medium voltage fuses
TECHNICAL DATA SHEETS	720106 24kV DIN medium voltage fuses
	720105 17.5kV DIN medium voltage fuses

	use
FUSE TYPE	TDQSJ

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

