



## Battery terminal pullers

11040

Product no. 71120012  
GTIN 4018754172825  
Model 11040/2


### Label.

Battery terminal pullers Spann-W.10-70mm x Spann-T.65mm

### Properties.

- two-armed, with a self-centring quick-action clamp and automatic feed
- for battery terminal clamps, smaller ball bearings, pulleys etc.
- for narrow, hard-to-reach spaces
- as force is applied through the spindle, the extractor hooks automatically apply increasing force to the part being extracted
- particularly suited to car electrics, compressed air system repairs and similar applications due to the compact design and small hooks
- zinc plated

## Product highlights.




### Adapted access geometry.

Heavy-duty puller hooks made of oil-hardened Chrome Alloy Steel with special access geometry for tight spaces. Custom radii for shafts and axes.

**For increased safety.**

Thoughtfully designed, die-forged and precisely machined, hardened and tempered on state-of-the-art machines - the STAHLWILLE puller range offers numerous products for a wide range of applications. For example, terminal pullers, pullers for ball joints, counter stays or ball joint extractors - always in premium quality.

**Technical drawing.****Technical attributes.**

Gr.	2
Antriebssechskant außen (mm)	12 mm
Anzahl Haken	2
max. Belastung	3,0 t
max. Drehmoment	35 N·m
Spanntiefe (h) mm	65 mm
Spannweite mm (w)	10-70 mm
Spindel-Gewindegröße	M10 x 110
Hakenfußbreite mm (b)	11 mm
Hakenfußtiefe mm (c)	11 mm
Stärke Hakenfußspitze mm (a)	2,5 mm

**Logistics data.**

Art.-Nr.	71120012
GTIN	4018754172825
Gewicht (g)	261 g
Volumen (verpackt, dm <sup>3</sup> )	0.3888 dm <sup>3</sup>
Packnorm	1
WEEE/ElektroG	nicht ear-pflichtig
Zolltarifnr.	82055980
Ursprungsland AWR	GERMANY
Ursprungsregion	Nordrhein-Westfalen
Tiefe mm (IFS)	120
Breite mm (IFS)	66
Höhe mm (IFS)	25
Gewicht (brutto, kg)	0,301
Gewicht PAP (kg)	0,026
Gewicht PVC (kg)	0,000
Länge (verpackt, mm)	150
Breite (verpackt, mm)	96

## Variants.

Art.-Nr.	Modell-Nr. (ERP)	Bezeichnung	GTIN
71120011	11040/1	Battery terminal puller Spann- W.10-60mm x Spann-T.45mm	4018754172818
71120012	11040/2	Battery terminal pullers Spann- W.10-70mm x Spann-T.65mm	4018754172825
71120013	11040/3	Battery terminal pullers Spann- W.10-100mm x Spann-T.80mm	4018754172832

## GTIN.



## Images.



**STAHLWILLE Eduard Wille GmbH**

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH, Wuppertal