



475-32-1
1/4" Bits Set 32 Pcs



PRODUCT DETAILS

- Includes 29 bits, 1 magnetic quick release bit holder, 1 socket adapter and 1 bit adapter
- 1/4" hex drive.
- For slotted, Phillips, Pozidriv, Torx® and hex head screws
- - Slotted: 4.0, 4.5, 5.5
- - Phillips: 2x PH1, 2x PH2, PH3, PH2G
- - Pozidriv: 2x PZ1, 2x PZ2, PZ3
- - Torx: T10, 2x T15, 2x T20, 2x T25, T27, T30, T40
- - Hex: H3, H4, H5, H6
- 1/4" female square to 1/4" female hex bit adapter
- 1/4" square socket adapter, ball type for regular nut driver socket (C 6.3)
- Magnetic quick release bit holder with locking system (E 6.3)
- Small, compact plastic case with belt clip
- In clamshell packaging
- DIN 3126, ISO 1173 Style C 6.3



PRODUCT ATTRIBUTES

Product			
475-32-1	32	30 x 65 x 105 mm	275 g

SET CONTENT



Bit Holder Square 1/4" with Hex 1/4"
105-48-1



1/4" Bit Hex 3, 25 mm, Box 5 Pcs
475-H3-1



1/4" Bit Hex 4, 25 mm, Box 5 Pcs
475-H4-1



1/4" Bit Hex 5, 25 mm, Box 5 Pcs
475-H5-1



1/4" Bit Hex 6, 25 mm, Box 5 Pcs
475-H6-1



1/4" Bit PH1, 25 mm, Box 10 Pcs
475-PH1-1



1/4" Bit PH2, 25 mm, Box 10 Pcs
475-PH2-1



1/4" Bit PH3, 25 mm, Box 10 Pcs
475-PH3-1



1/4" Bit PZ1, 25 mm, Box 10 Pcs
475-PZ1-1



1/4" Bit PZ2, 25 mm, Box 10 Pcs
475-PZ2-1



1/4" Bit PZ3, 25 mm, Box 10 Pcs
475-PZ3-1



1/4" Bit T10, 25 mm, Box 10 Pcs
475-T10-1



1/4" Bit T15, 25 mm, Box 10 Pcs
475-T15-1



1/4" Bit T20, 25 mm, Box 10 Pcs
475-T20-1



1/4" Bit T25, 25 mm, Box 10 Pcs
475-T25-1



1/4" Bit T27, 25 mm, Box 10 Pcs
475-T27-1



1/4" Bit T30, 25 mm, Box 5 Pcs
475-T30-1



1/4" Bit T40, 25 mm, Box 5 Pcs
475-T40-1



1/4" Bit Slotted 4.5, 25 mm, Box 10
Pcs
475-4.5-1



1/4" Bit Slotted 4.0, 25 mm, Box 10
Pcs
475-4-1



1/4" Bit Slotted 5, 25 mm, Box 10 Pcs
475-5.5-1



1/4" Socket Adaptor, 25 mm
475A-25-1



Quick Release Bit Holder 1/4" 60 mm
475A-60QR-1