

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0192210412](#)  
**Status:** **Active**  
**Overview:**  
**Description:** Compression Ring Tongue Terminal for 4/0 AWG Wire, Stud Size 5/16" (M8), Plated, Barrel Length 19.05mm

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series [19221](#)  
 Comments Heavy Duty  
 Crimp Quality Equipment Yes  
 Overview battery\_cable\_lugs  
 Product Name Battery Cable Lug  
 Taxonomy Ring and Spade Terminals  
 Type Ring  
 UPC 800753064966

**Physical**

Barrel Type Closed  
 Insulation None  
 Material - Plating Mating Tin  
 Net Weight 38.175/g  
 Packaging Type Bag  
 Plating min - Mating 4.064µm  
 Plating min - Termination 4.064µm  
 Stud Size 5/16" (M8)  
 Termination Interface: Style Crimp or Compression  
 Wire Size AWG 4/0

**Material Info**

Engineering Number BCL-40516-PL

**Reference - Drawing Numbers**

Product Specification PS-19901-017-001, PS-19902-011-001,  
 PS-19902-013-001, PS-19902-017-001  
 Sales Drawing SD-19221-011-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 D(2020)9139-DC (19  
 Jan 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19221](#) Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Hand Crimp Tool for Eyelet Style Copper Lug Terminals 8-4/0 AWG	<a href="#">192840034</a>
Manual Putt Pump Hydraulic System, Die set required	<a href="#">192860117</a>
Die Set (large) for the HHLS Hydraulic Crimper	<a href="#">192900031</a>
Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	<a href="#">192940008</a>
Hydraulic Dieless Crimping Tool	<a href="#">638161700</a>
Square "Din" Style Die Set for BCL and VersaKrimp Un-insulated Ring Tongue Terminals and Splices, 4/0 AWG	<a href="#">640038370</a>

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**