



**Part Number :** 334713301

**Product Description :** MX150 Mat-Sealed Female Connector Assembly, Single Row, 3 Circuits, Keying Option A, Black

**Series Number :** 33471

**Status :** Active

**Product Category :** Connector Housings

**Engineering Number :** CVP33471-3301



## Documents & Resources

### Drawings

[334713301\\_sd.pdf](#)

[PK-31300-635-001.pdf](#)

### 3D Models and Design Files

[334713301\\_stp.zip](#)

### Specifications

[AS-33472-100-001.pdf](#)

[AS-33472-100-CH-001.pdf](#)

[AS-33472-100-FR-001.pdf](#)

[AS-33611-001-001.pdf](#)

[AS-34711-001-001.pdf](#)

[AS-34711-001-CH-001.pdf](#)

[PS-33471-000-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant
China RoHS	Compliant per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Dodecamethylcyclohexasiloxane;

	Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Connector Housings
Series	33471
Description	MX150 Mat-Sealed Female Connector Assembly, Single Row, 3 Circuits, Keying Option A, Black
Application	Power, Wire-to-Wire, Automotive
Comments	No Connector Position Assurance (CPA)
Product Name	MX150
UPC	191128449809

### Agency

UL	E29179
----	--------

### Physical

Circuits (maximum)	3
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	7.700/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
MX150 Mat-Sealed Single Row Male Connector Assemblies	<u>33481</u>

### Use with Part(s)

Description	Part Number
MX150 Sealed Receptacle Cavity Plug	<u>343454001</u>
MX150 Backshell for Male Sealed Connector Assembly, 6 Circuit, with Rib	<u>349500610</u>
MX150 Backshell for Male Sealed Connector Assembly, 6 Circuit, without Rib	<u>349500620</u>
MX150 Female Terminals	<u>33001</u>
MX150 Female Terminals	<u>33012</u>

This document was generated on Jul 09, 2025