

## Convenio - Electrical Accessories

### CONVENIO CONNECTOR

0043335



#### Range Features

- Convenio is a range of products that create a modular lighting system covering most of spot, linear and area lighting applications
- Unified electrical and mechanical interface allows the customer to create a variety of lighting schemes
- Contemporary and minimalist ultra slim design
- Seamless mounting brackets for easy installation
- Convenio Linear is a slim homogenous LED linear light used for undercabinet, wall and ceiling lighting applications
- Convenio Linear Spot light is used for wall washing or suspended table lamp applications
- Convenio Spot is a LED Spot light used for accent lighting with a high lumen output of 400lm
- Various accessories (flat corner, Inside corner, outside corner, dimmable sensor switch) available for personalisation
- Available in warm white 3000K

## PRODUCT OVERVIEW

<b>Certifications</b>	CE
<b>Colour temperature (K)</b>	3000
<b>Colour</b>	White/Silver
<b>CRI (Ra)</b>	80
<b>EAN code</b>	5410288433356
<b>IP rating</b>	IP20
<b>Light colour</b>	Warm white
<b>Mount</b>	Surface mounted
<b>Ordering number</b>	0043335
<b>Technology</b>	LED
<b>Colour consistency (SDCM)</b>	5 Step

## DATA TABLE

### General data

<b>Certifications</b>	CE
<b>EAN code</b>	5410288433356
<b>Environment</b>	Internal
<b>General application</b>	Residential; Hospitality; Retail
<b>Mount</b>	Surface mounted
<b>Ordering number</b>	0043335

## Convenio - Electrical Accessories

### CONVENIO CONNECTOR

**0043335**

<b>Range features</b>	<p>Convenio is a range of products that create a modular lighting system covering most of spot, linear and area lighting applications</p> <p>Unified electrical and mechanical interface allows the customer to create a variety of lighting schemes</p> <p>Contemporary and minimalist ultra slim design</p> <p>Seamless mounting brackets for easy installation</p> <p>Convenio Linear is a slim homogenous LED linear light used for undercabinet, wall and ceiling lighting applications</p> <p>Convenio Linear Spot light is used for wall washing or suspended table lamp applications</p> <p>Convenio Spot is a LED Spot light used for accent lighting with a high lumen output of 400lm</p> <p>Various accessories (flat corner, Inside corner, outside corner, dimmable sensor switch) available for personalisation</p> <p>Available in warm white 3000K</p>
<b>Product name</b>	CONVENIO CONNECTOR
<b>Technology</b>	LED
<b>Product features</b>	LED connector accessory, will link any CONVENIO product, length 150mm.

#### Optical data

<b>Colour temperature (K)</b>	3000
<b>CRI (Ra)</b>	80
<b>Light colour</b>	Warm white
<b>Colour consistency (SDCM)</b>	5 Step

#### Physical data

<b>Colour</b>	White/Silver
<b>Height (mm)</b>	4.9
<b>IP rating</b>	IP20
<b>Length (mm)</b>	150
<b>Width (mm)</b>	19

#### Electrical data

<b>Ta rating (°C)</b>	-20 to +46
-----------------------	------------

## TECHNICAL DRAWINGS

