



# 1605

## Air

Peli™ Air cases are the first in a series of remarkable innovations engineered by Peli, the pioneers of protective cases. For over 45 years Peli has designed and crafted the most influential protective cases in the world, and we're just getting started. With the launch of the Peli™ Air line of cases, we're redefining the future of protection with a remarkable union of light and tough.

- Automatic pressure equalization valve - balances interior pressure, keeps water out
- Fold down over-molded handle
- Stainless steel padlock protectors
- Press and Pull™ Latches
- Limited Lifetime Warranty
- Super-light proprietary HPX<sup>2</sup>™ Polymer - up to 40% lighter
- Waterproof O-ring seal
- User-customizable Pick N Pluck™ foam
- Waterproof, crushproof, dustproof
- IP67 & MIL-SPEC certified



## CONFIGURATIONS



**1605**  
Standard



**1605NF**  
No Foam



**1605WD**  
With Padded Dividers



**1605TP**  
With TrekPak Divider System



**1605WF**  
With Foam

## DIMENSIONS

|                              |                                               |
|------------------------------|-----------------------------------------------|
| <b>Interior (L×W×D)</b>      | 26.00 x 14.00" x 8.38 (66 x 35.6 x 21.3 cm)   |
| <b>Exterior (L×W×D)</b>      | 28.87 x 16.77" x 9.12 (73.3 x 42.6 x 23.2 cm) |
| <b>Lid Depth</b>             | 2.00" (5.1 cm)                                |
| <b>Bottom Depth</b>          | 6.38" (16.2 cm)                               |
| <b>Total Depth</b>           | 8.38" (21.3 cm)                               |
| <b>Int Volume</b>            | 1.77 ft <sup>3</sup> (0.05 m <sup>3</sup> )   |
| <b>Padlock Hole Diameter</b> | 0.31" (0.8 cm)                                |

## MATERIALS

|                   |                                                 |
|-------------------|-------------------------------------------------|
| <b>Body</b>       | Proprietary Polypropylene Blend                 |
| <b>Latch</b>      | ABS                                             |
| <b>O-Ring</b>     | EPDM                                            |
| <b>Purge Body</b> | ABS                                             |
| <b>Purge Vent</b> | Hi-Flow Gore-Tex 3 Micron Hydrophobic Non-Woven |

COLOURS

|                                                                                         |                                                                                          |                                                                                          |                                                                                            |
|-----------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------|
|  Black |  Orange |  Silver |  Yellow |
|-----------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------|


WEIGHT

|                         |                       |
|-------------------------|-----------------------|
| <b>Weight With Foam</b> | 11.61 lbs (5.27 kg)   |
| <b>Weight Empty</b>     | 9.28 lbs (4.21 kg)    |
| <b>Buoyancy</b>         | 112.90 lbs (51.21 kg) |

TEMPERATURE

|                            |                |
|----------------------------|----------------|
| <b>Minimum Temperature</b> | 0°F (-17.8 °C) |
| <b>Maximum Temperature</b> | 140°F (60 °C)  |

ACCESSORIES

|                                                                                     |                                                                                     |                                                                                   |                                                                                    |                                                                                     |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|    |    |  |  |  |
| <b>1605AirFS</b><br>4 pc. Replacement Foam Set                                      | <b>1605AirDS</b><br>Padded Divider Set                                              | <b>1605TP-KIT</b><br>TrekPak Case Divider Kit                                     | <b>1605TPKIT</b><br>TrekPak Case Divider Kit                                       | <b>1605TPDIV</b><br>Extra TrekPak Dividers                                          |
|  |  |                                                                                   |                                                                                    |                                                                                     |
| <b>1506TSA</b><br>TSA Lock                                                          | <b>1500D</b><br>Desiccant Silica Gel                                                |                                                                                   |                                                                                    |                                                                                     |