

Features

- 19" Device Compatibility
- Ventilation
- Suitable for 19" accessory installation.
- Cable entry options available.
- Optional cable entry at the back with plastic cover.
- Brush Cable Entry at the top.

RS PRO Server Cabinets

RS Stock No.: 0749210



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *Areas of use: Offices (home, workplace), Branches (banks, government offices), Schools, Hospitals, Factories*
- *Purposes of use: Installation and setup of small systems, Intermediate distribution terminal, Floor distribution in network systems, Wall-mounted network installation applications*

General Specifications

Rack Units	7U
Type	Wall Mount
External Case Material	Steel
Base Material	Metal
Surface Finish	Electrostatic Powder Coating
Mounting	Wall type
Cabinet Size	Width: 535.00mm Depth: 400.00mm
Special Features	Drop Sticker Logo
Colour	RAL9005
Glass	Tempered
Ventilated	Yes
Fan Included	No
Adjustable Feet	No
EMC Shielding	No

Mechanical Specifications

External Dimensions	535.00mm x 400.00mm x 348.50mm
External Height	348.50mm
External Width	535.00mm
External Depth	400.00mm
Internal Depth	382.50mm
Weight	10.50kg

Protection Category

IP Rating	IP20
-----------	------

Approvals

Declarations	MFR Declaration of Conformity
Standards Met	CE Marking / 2014/30/EU / 2014/35/EU / 2011/65/EU (RoHS II) / EN 61587-1 / EN IEC 60297 Series / EN IEC 60917 Series / EIA/ECA-310-D/E / EN IEC 62262

Similar Products

Stock No.	Brand	Colour	Material	Measurements
0749209	RS PRO	RAL9005	1mm Steel	H: 215.20mm D: 400.00mm
0749213	RS PRO	RAL9005	1mm Steel	H: 215.20mm D: 600.00mm
0749214	RS PRO	RAL9005	1mm Steel	H: 348.50mm D: 600.00mm
0749211	RS PRO	RAL9005	1mm Steel	H: 437.40mm D: 400.00mm
0749215	RS PRO	RAL9005	1mm Steel	H: 437.40mm D: 600.00mm
0749212	RS PRO	RAL9005	1mm Steel	H: 570.80mm D: 400.00mm
0749217	RS PRO	RAL9005	1mm Steel	H: 570.80mm D: 600.00mm

Accessories

Stock No.	Brand	Colour	Material	Mounting location in the cabin
0749232	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749233	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749234	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749236	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749239	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749240	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749241	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749242	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749243	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749245	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749248	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749249	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails

0749251	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749252	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749253	RS PRO	RAL9005	1.0mm Steel	Top Chassis
0749254	RS PRO	RAL9005	1.0mm Steel	Top Chassis
0749255	RS PRO	RAL9005	1.0mm Steel	Top Chassis
0749256	RS PRO	RAL9005	1.0mm Steel	Top Chassis
0749225	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749226	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749246	RS PRO	RAL9005	Steel	19" Device Mounting Rails
0749247	RS PRO	RAL9005	Steel	19" Device Mounting Rails

