

CA-000000080DN - Housing for circular connector



1621408

<https://www.phoenixcontact.com/in/products/1621408>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Housing for circular connector, series: CA, straight, shielded: yes, Screw locking mechanism, cable diameter range: 3 mm ... 14.5 mm, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1244390

Commercial data

Item number	1621408
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	ABRAEE
GTIN	4046356919333
Weight per piece (including packing)	90.2 g
Weight per piece (excluding packing)	84.13 g
Customs tariff number	85366990
Country of origin	DE

CA-000000080DN - Housing for circular connector



1621408

<https://www.phoenixcontact.com/in/products/1621408>

Technical data

Notes

Order information:	Order contact inserts separately
--------------------	----------------------------------

Product properties

Product type	Circular connector housing
Series	CA
Type	on the cable side

Connector

Housing

Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Type of locking	Screw locking mechanism
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

Seal

External cable diameter	3 mm ... 14.5 mm
Seal material	NBR

CA-000000080DN - Housing for circular connector



1621408

<https://www.phoenixcontact.com/in/products/1621408>

Classifications

ECLASS

ECLASS-13.0	27440224
-------------	----------

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	72b7c6e9-7f59-4e11-845f-aa0dce825c84

CA-000000080DN - Housing for circular connector

1621408

<https://www.phoenixcontact.com/in/products/1621408>



Accessories

SF-Z0028 - Torque screwdriver

1607456

<https://www.phoenixcontact.com/in/products/1607456>

Torque screwdriver, series: RC, UC, SH, SF



SF-Z0027 - Hook wrench

1607455

<https://www.phoenixcontact.com/in/products/1607455>

Hook wrench, series: RC, UC, RF, SF



CA-000000080DN - Housing for circular connector



1621408


<https://www.phoenixcontact.com/in/products/1621408>

RF-Z0014 - Color coding

1620588

<https://www.phoenixcontact.com/in/products/1620588>

Color coding, color: green



RF-Z0015 - Color coding

1620592

<https://www.phoenixcontact.com/in/products/1620592>

Color coding, color: orange



CA-000000080DN - Housing for circular connector

1621408

<https://www.phoenixcontact.com/in/products/1621408>



RF-Z0016 - Color coding

1620593

<https://www.phoenixcontact.com/in/products/1620593>

Color coding, color: black



CA-Z0077 - Metal protective cap

1627224

<https://www.phoenixcontact.com/in/products/1627224>



Metal protective cap, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1245447

CA-000000080DN - Housing for circular connector

1621408

<https://www.phoenixcontact.com/in/products/1621408>



PROT-M23-SG-IT-IP20 - Plastic protective cap

1577206

<https://www.phoenixcontact.com/in/products/1577206>

Plastic protective cap, M23, series: CA, RC, RF, UC, RM



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in