

# A-INSP-PG29-65N-P-LG - Screw plug



1424525

<https://www.phoenixcontact.com/in/products/1424525>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Screw plug, material for screw connection: PA, connecting thread: Pg29, color: lightgray  
RAL 7035



## Commercial data

Item number	1424525
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF7
Product key	AF7DZX
Catalog page	Page 703 (C-2-2019)
GTIN	4055626374307
Weight per piece (including packing)	6.45 g
Weight per piece (excluding packing)	6.45 g
Customs tariff number	39269097
Country of origin	DE

# A-INSP-PG29-65N-P-LG - Screw plug



1424525


<https://www.phoenixcontact.com/in/products/1424525>

## Technical data

### Product properties

Product type	Plug for cable screw gland
--------------	----------------------------

### Dimensions

Dimensional drawing		
Length	12 mm	
Length of the connecting thread	8 mm	
Length without connecting thread	4 mm	
Diameter	37 mm	
	44 mm	
Connecting thread diameter	37 mm	
Thread type connection side	Pg29	

### Material specifications

Material	PA
Seal material O-ring	EPDM
Material for screw connection	PA

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 100 °C

# A-INSP-PG29-65N-P-LG - Screw plug


1424525

<https://www.phoenixcontact.com/in/products/1424525>



## Drawings

Dimensional drawing



Dimensional drawing

# A-INSP-PG29-65N-P-LG - Screw plug



1424525

<https://www.phoenixcontact.com/in/products/1424525>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1424525>



**EAC**

Approval ID: EAC-Zulassung

# A-INSP-PG29-65N-P-LG - Screw plug



1424525

<https://www.phoenixcontact.com/in/products/1424525>

## Classifications

### ECLASS

ECLASS-11.0	23111190
ECLASS-12.0	23111190
ECLASS-13.0	23111190

### ETIM

ETIM 9.0	EC000032
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# A-INSP-PG29-65N-P-LG - Screw plug



1424525

<https://www.phoenixcontact.com/in/products/1424525>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

# A-INSP-PG29-65N-P-LG - Screw plug

1424525

<https://www.phoenixcontact.com/in/products/1424525>



## Accessories

### A-INL-PG29-P-LG - Counter nut

1424554

<https://www.phoenixcontact.com/in/products/1424554>

Counter nut, connecting thread: Pg29, color: light gray



---

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.  
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420  
[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)