


Product datasheet

Specifications



MOUNTING PLATE VIGI NSX WITHDRAWABLE ALL CONTROLS-3/4P 250A HORIZONTAL WIDTH650

LVS03415

EAN Code: 3606481874290

Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle
installation description	Cubicle - width 650 mm depth 400 mm
Installed device	ComPact: drawout NSX100...160 without earth leakage protection - control: toggle - horizontal installation ComPact: drawout NSX100...160 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: drawout NSX100...160 without earth leakage protection - control: motor mechanism - horizontal installation ComPact: drawout NSX250 without earth leakage protection - control: toggle - horizontal installation ComPact: drawout NSX250 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: drawout NSX250 without earth leakage protection - control: motor mechanism - horizontal installation ComPact: drawout NSX100...160 with earth leakage protection - control: toggle - horizontal installation ComPact: drawout NSX100...160 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: drawout NSX100...160 with earth leakage protection - control: motor mechanism - horizontal installation ComPact: drawout NSX250 with earth leakage protection - control: toggle - horizontal installation ComPact: drawout NSX250 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: drawout NSX250 with earth leakage protection - control: motor mechanism - horizontal installation
Poles description	1 x 3P: drawout NSX100...160 horizontal installation 1 x 4P: drawout NSX100...160 horizontal installation 1 x 3P: drawout NSX250 horizontal installation 1 x 4P: drawout NSX250 horizontal installation
Number of vertical modules [50 mm]	5 module(s): NSX100...160 without earth leakage protection , direct in 650 mm Widecubicle 5 module(s): NSX250 without earth leakage protection , direct in 650 mm Widecubicle 5 module(s): NSX100...160 with earth leakage protection , direct in 650 mm Widecubicle 5 module(s): NSX250 with earth leakage protection , direct in 650 mm Widecubicle
Standards	IEC 61439-2
Product certifications	ASTA

Complementary

Material	Sheet steel
----------	-------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Textured Matt
Colour	White (RAL 9003)
Width	575 mm
Height	245 mm
Net weight	2.78 kg
Functional unit	650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 without drawout direct front rotary handle horizontal 3P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 without drawout motor mechanism horizontal 3P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 without drawout direct front rotary handle horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 without drawout motor mechanism horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 without drawout toggle horizontal 3P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 without drawout toggle horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX250 without drawout direct front rotary handle horizontal 3P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX250 without drawout motor mechanism horizontal 3P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX250 without drawout direct front rotary handle horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX250 without drawout motor mechanism horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX250 without drawout toggle horizontal 3P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX250 without drawout toggle horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 with drawout direct front rotary handle horizontal 3P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 with drawout motor mechanism horizontal 3P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 with drawout direct front rotary handle horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 with drawout motor mechanism horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 with drawout toggle horizontal 3P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX100...160 with drawout toggle horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX250 with drawout direct front rotary handle horizontal 3P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX250 with drawout motor mechanism horizontal 3P 1 direct 5 12.5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.3 cm
Package 1 Width	25 cm
Package 1 Length	57.5 cm
Package 1 Weight	2.803 kg
Unit Type of Package 2	S04
Number of Units in Package 2	4
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	11.91 kg

Unit Type of Package 3	P12
Number of Units in Package 3	16
Package 3 Height	43 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	59 kg

Logistical informations

Country of origin	IN
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	4758f26b-dbf8-498a-a5c2-4de140d6aa9a
REACH Regulation	REACH Declaration
Halogen content performance	Halogen free plastic parts product
PVC free	Yes

Use Again

Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions

