

9.8 ft. (3m) USB-C to DVI Cable - 1920 x 1200 - Black

Product ID: CDP2DVI3MBNL



This USB-C to DVI cable lets you connect your Thunderbolt 3 or USB Type-C enabled device to a DVI computer monitor with just one cable, providing you with a convenient, clutter-free solution.

Astonishing Picture Quality

The USB-C to DVI adapter cable lets you harness the video capabilities that are built into your USB-C connection, to deliver astonishing picture quality at resolutions up to 1920 x 1200.

Plus, the USB-C video cable is backward compatible with 1080p displays, which makes it a great accessory for home, office or other work environments.

Clutter-Free Installation

At 9.8 ft. (3 m) in length, this computer monitor cable delivers a compact connection that eliminates excess adapters and cabling, ensuring a tidy, professional installation. For shorter installations, we also offer a 3.3 ft. (1 m) ([CDP2DVIMM1MB](#)) and a 6.6 ft. (2 m) ([CDP2DVIMM2MB](#)) USB-C to DVI cable, enabling you to choose the right cable length for your custom installation needs.

Hassle-Free Connection

The reversible USB-C connector offers an easy and convenient connection. To ensure easy operation and installation, this USB-C to DVI cable works with both Windows and Mac computers and supports easy plug-and-play installation.

CDP2DVI3MBNL is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Note: Your USB-C port must support DisplayPort over USB-C (DP Alt Mode) in order to work with this adapter.

Certifications, Reports and Compatibility



Applications

- Connect USB-C or Thunderbolt 3 devices to DVI displays
- Ideal for home office or work desk environments
- Experience enhanced imaging with support for resolutions up to 1920x1200

Features

- Get astonishing picture quality with support for video resolutions up to 1920 x 1200
- Reduce clutter with a USB-C to DVI adapter and display cable, in-one
- Make the perfect connection with a computer monitor cable that works with any USB-C enabled laptop
- Hassle-free connectivity with the reversible USB-C connector
- Compatible with Thunderbolt 3 and USB 3.1 Type-C ports that support DP Alt Mode

Hardware	Warranty	3 Years
	Adapter Style	Cable Adapters
	AV Input	USB Type-C
	AV Output	DVI
	Chipset ID	VIA/VLI - VL100 Parade - PS171
	Ports	1
Performance	Maximum Digital Resolutions	1920x1200
	Supported Resolutions	1024x768 1280x720 (High-definition 720p) 1920x1080 (High-definition 1080p) 1920x1200
Connector(s)	Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode Male Input 1 - DVI-D (25 pin) Male Output
Special Notes / Requirements	Note	Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.
	System and Cable Requirements	Some dual-link DVI monitors manufactured prior to 2014 may have limited resolutions support when used with this adapter. This adapter is not compatible for use with the Apple Cinema Display.
Environmental	Humidity	5%-90% RH (no condensation)
	Operating Temperature	0°C to 45°C (32°F to 113°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
Physical Characteristics	Cable Length	3 m [9.8 ft]
	Color	Black
	Product Height	1 cm [0.4 in]
	Product Length	3 m [9.8 ft]
	Product Width	20 mm [0.8 in]
	Weight of Product	141 g [5 oz]
Packaging Information	Package Height	10 mm [0.4 in]
	Package Length	22.5 cm [8.9 in]
	Package Width	12.5 cm [4.9 in]

	Shipping (Package) Weight	0.1 kg [0.3 lb]
What's in the Box	Included in Package	1 - USB-C to DVI cable

Product appearance and specifications are subject to change without notice.