




---

 PRODUCT-DETAILS

## 2601/2 WDI

Switch Rocker/button, 2-pole switch with Not included blue - Busch-Duro 2000 WDI




---

### General Information

Extended Product Type	2601/2 WDI
Product ID	2CKA001084A0821
EAN	4011395026809
Catalog Description	Switch Rocker/button, 2-pole switch with Not included blue - Busch-Duro 2000 WDI
Long Description	For difficult on-site conditions such as aggressive media (ammonia, petrol, oils, greases, cleaning agents in usual concentrations) we recommend the use of cable entries 2070/2071.

---

### Installation

Instructions and Manuals	No document needed
Wiring Diagram	2CKA000097E0043
Mounting Type	Surface Mounted
Type of Fastening	Mounting with Screw
Modular Components Included	Complete Device

## Environmental

Degree of Protection	IP66
----------------------	------

## Technical

Data Sheet, Technical Information	No document needed
Function	Function lighting: Control and orientation
Number of Rocker Switches	1
Wiring Configuration	2-pole switch
Actuator Type	Rocker/button
Lamp Type	Not included
Illumination	Optional
Terminal Type	Screwless Terminals

## Electrical

Rated Voltage ( $U_r$ )	250 V
Rated Current ( $I_n$ )	16 A
Power Watt	LEDi / CFLi 200 W

## Design

Design Range	Busch-Duro 2000 WDI
Surface Finishing	Untreated Matt
Material	Thermoplastic
Label Space Provided	Without Label Space
RAL Number	Similar to RAL 5010
Color	blue

## Dimensions

Product Net Width	74 mm
Product Net Height	93 mm
Product Net Depth / Length	54 mm
Product Net Weight	160 g
Dimension Diagram	2CKA000097E0614

## Material Compliance

RoHS Declaration	2CKA200000E0289
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
REACH Declaration	2CKA309999E9999
REACH Information	True - contains substances > 0.1 mass percentage
REACH Date	20250901
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363
SCIP	a61b1624-9949-4c53-9475-730eb8a4ae86 Germany

Simplified SCIP	a61b1624-9949-4c53-9475-730eb8a4ae86 Germany
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Consumer

## Certificates and Declarations

Declaration of Conformity - CE	2CKA100000E0191
EU Data Act Applicability and Compliance	Not Applicable

## External Classifications and Standards

ETIM 9	EC001590 - Installation switch
ETIM 10	EC001590 - Installation switch
eClass	V11.0 : 27144053

## Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
2CKA001784A0321	Illumination set for Switch/push button Orange Neon lamp, 1 mA, 230 V	8346-1	1	piece
2CKA001784A0719	Illumination set for Switch/push button White Incandescent lamp, 40 mA, 24 V AC/DC	8358	1	piece
2CKA001784A0529	Illumination set for Switch/push button White Incandescent lamp, 40 mA, 12 V	8335-1	1	piece
2CKA001784A0016	Illumination set for Switch/push button Orange Neon lamp, 0.6 mA, 230 V	8332-1	1	piece
2CKA001761A0808	Cable Entry blue	2081	1	piece
2CKA001761A0782	Cable Entry blue	2079	1	piece
2CKA001761A1368	Cable Entry grey	2070	1	piece
2CKA001761A1376	Cable Entry grey	2071	1	piece

## Categories

Low Voltage Products and Systems → Wiring Accessories - Light Switch Ranges → Surface Mounted Range → Mechanical Controls

