


11967 MFH-3-3/4 Solenoid valve - Series: All



11967 MFH-3-3/4 Solenoid valve - Series: All

Pos.	Part no.	Type	Note	Qty.	Unit
A	384019	MFH-3-3/4 /-S Set of wearing parts	Spare parts: 7, 10, 12, 14, 15, 17, 19, 22 Attention, please order position 23 as well	1	PC
1	208281	MSSD-F Socket		1	PC
2	209407	M 8X0,75 FUER D03 Knurled nut		1	PC
3	200589	A 8 DIN 137 Spring washer		1	PC
4	4526	MSFG-12 Solenoid coil	Please order this position from the catalogue as an accessory.	1	PC
5	101006	KPL.M.ANKER O.SPULE Armature tube		1	PC
6	209354	ISO 4762-M6X14-10.9 Socket head screw	Tightening torque 3.5 Nm / 2.6 lbf ft	2	PC
7		B-5X1,5-N-NBR75 O-ring ISO3601	Not available separately, see position A Grease using during assembly. See position 22	1	PC
8	385843	MFH-3-3/4 Bolt		1	PC
9	107082	MFH-3-3/4 Cover		1	PC
10		B-60X2-N-NBR70 O-ring ISO3601	Not available separately, see position A Grease using during assembly. See position 22	1	PC
11	200719	DIN 934-M8-8 Hex nut	Tightening torque 3.5 Nm / 2.6 lbf ft Use locking compound. See position 23	1	PC
12		MFH-3-3/4 Piston	Not available separately, see position A Grease using during assembly. See position 22	1	PC
13	222906	MFH-3-3/4 Spindle		1	PC
14		MFH-3-3/4 PERBUNAN Seal	Not available separately, see position A Grease using during assembly. See position 22	1	PC
15		B-9X1,5-N-NBR75 O-ring ISO3601	Not available separately, see position A Grease using during assembly. See position 22	1	PC
16		MFH-3-3/4 Housing	Not available	1	PC
17		MFH-3-3/4 Sealing disc	Not available separately, see position A Use locking compound. See position 23	1	PC
18	213292	MFH-5-1/2 Compression spring		1	PC
19		B-54X3-N-NBR75 O-ring ISO3601	Not available separately, see position A Grease using during assembly. See position 22	1	PC
20	222516	MFH-3-3/4 Cover		1	PC
21	401261	DIN 472-60X2 Retaining ring		1	PC
22	397446	LUB-KB2-SILIKONFREI-20ML Lubricating grease		1	PC
23	8181256	CYBERBOND TM44 TB1ML Adhesive bonding agent	Not included in wearing-parts kit	1	PC