


P-881-ESD/891-ESD

ESD CUSHION TWEEZERS



ESD safe plastic offers comfort and control of static electricity.

- Resilient elastomer grip fits comfortably in your hand.
- Dimension: 150mm
- Material: Elastomer (grip), Stainless (tweezers)
- Weight: P-881-ESD 26g
P-891-ESD 32g





P-845

ESD CUSHION GRIP



With this ESD safe cover you can make your standard tweezer ESD safe.

- The cover allows for ESD safe plastic for handling and to cover the tweezer for safety while you carry
- Dimension: 150mm (Include cap)
- Material: Elastomer (conductive)
- Weight: 9g
- Accessory: Protection cap
- Applicable model: P-850-P-852, P-891-P-894, P-86-125, P-87, P-88, P-881, P-882, P-887, But can not CAP for P-852/882/887.



Applicable tweezers size.
8.5~10mm
110~130mm

Tweezers of over 130mm and bent-type can not use.

ESD TWEEZERS



- Extra sharp points. (0.4mm) ESD safe replacement tips.
- Specially designed for the fine electronics industry.

- Material (Tip): PEEK
- Material (Handle): Stainless Steel
- Tip color: Black
- Heat-resistant temperature (tips): 160°C



P-814-S

- O.A.L.: 125mm
- Point-size: 0.4mm
- Weight: 20g
- Tip: P-814S-1



Replacement Parts

P-814S-1 TWEEZERS TIP

- Material: PEEK
- Tip color: Black
- Point-size: 0.4mm
- Heat-resistant temperature: 160°C
- 2/pack



P-815-S


- O.A.L.: 125mm
- Point-size: 1.2mm
- Weight: 20g
- Tip: P-815S-1



Replacement Parts


P-815S-1 TWEEZERS TIP

- Material: PEEK
- Tip color: Black
- Point-size: 1.2mm
- Heat-resistant temperature: 160°C
- 2/pack



P-816-S

- O.A.L.: 115mm
- Point-size: R1.2mm
- Weight: 20g
- Tip: P-816S-1



Replacement Parts

P-816S-1 TWEEZERS TIP

- Material: PEEK
- Tip color: Black
- Point-size: R1.2mm
- Heat-resistant temperature: 160°C
- 2/pack



CUTTERS
WIRE STRIPPERS
CRIMPERS
TWEEZERS
SCREWDRIVERS & WRENCHES
METAL WORKING TOOLS
CASES & BAGS
TOOL KITS
SOLDERING TOOLS
DESOLDERING TOOLS
MEASURING INSTRUMENTS
MICROSCOPES & MAGNIFIERS
STATIC CONTROL
CLEAN ENVIRONMENT
CHEMICALS
MAINTENANCE TOOLS