



Multi Purpose



Light Duty

The perfect combination of comfort, dexterity with ESD/Touchscreen compatibility

- Ultra-thin coating provides increased sensitivity for precision tasks
- Ansell FORTIX™ Abrasion Resistance Technology (New & Improved)
 - Provides long lasting protection in abrasive environments
 - 20% more breathable vs standard safety gloves for cooler, drier hands
- Ansell ZONZ™ Comfort Fit Technology for enhanced fit and feel
- Benefits from proprietary washing process to deliver a cleaner, more comfortable glove
- Clean and Skin Friendly : OekoTex® Certified and Dermatologically tested by Dermatest®
- ESD certified according to EN16350 : 2014
- Touchscreen Technology* for use on consumer and industrial touchscreens



Industries

- Aerospace
- Automotive
- Machinery and Equipment
- Logistics
- Industrial
- White Goods

Applications

- General handling
- Mounting and dismantling
- Machine tool operation
- Quality inspection
- Applications requiring dexterity and precision
- Compatible with consumer and industrial touchscreens
- Environments requiring ESD protection
- Warehouse and logistics operations

HyFlex[®]

ADVANCED MECHANICAL PROTECTION

11-819 ESD

The ultimate ESD/Touchscreen glove

Key Features

- **ESD Certified:** HyFlex[®] 11-819 is a safety glove with ESD functionality certified to EN 16350:2014, protecting products against electrostatic discharge. In addition, as part of a grounding chain they can be used in explosion hazard zones (ATEX ATmosphères EXplosives).
- **Touchscreen compatible:** It's touchscreen functionality allows the wearer to work with multiple touchscreen devices while keeping safety gloves on
- **Long Lasting Protection:** The FORTIX[™] nitrile foam coating offers excellent grip and long lasting protection, reducing the total cost of ownership
- **Barehand-like tactility:** The seamless 18 gauge nylon and spandex liner combined with the ultra-thin FORTIX[™] coating provides protection while maintaining bare hand sensitivity for tasks that require dexterity and precision
- **Comfortable and Clean:** The careful selection of materials, the Ansell ZONZ[™] Comfort Fit Technology and proprietary washing process makes the HyFlex[®] 11-819 a clean, ultra breathable and highly comfortable glove
- **Skin Friendly:** Dermatologically approved by Dermatest[®] and certified by OEKO-TEX[®]

Technologies



FORTIX[™]

Abrasion Resistance Technology



Touchscreen Compatible



ZONZ[™]

Comfort Fit Technology

Performance Standards & Regulatory Compliance

REACH Compliant



3121A



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex [®] 11-819 ESD	Finishing: Palm dipped Coating Material: Fortix [™] Foam Nitrile Liner Material: Nylon, Spandex, Carbon Cuff Style: Knitwrist	18	6, 7, 8, 9, 10, 11	195-255 mm	Blue	• 12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jaijan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, [®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

