



Part Number : [988161011](#)
Product Description : NSCC Unsealed Female
Housing, 10 Circuits, Dual Row, Black, Version 2 with
Ear
Series Number : 98816
Status : Not Recommended For New Design
Product Category : Connector Housings
Engineering Number : 18501EV10M1



Documents & Resources

Drawings
[988161011 sd.pdf](#)
Specifications
[AS-98816-001-001.pdf](#)
[PK-98816-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	Connector Housings
Series	98816
Description	NSCC Unsealed Female Housing, 10 Circuits, Dual Row, Black, Version 2 with Ear
Application	Power, Wire-to-Wire
Comments	Pitch Center Spacing: Horizontal Pitch 3.33mm, Vertical pitch 6.00mm
Product Name	NSCC
UPC	822348761333

Physical

Circuits Detail	10x1.5mm female terminals
Circuits (maximum)	10
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	5.000/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No

Pitch - Mating Interface	3.33mm, 6.00mm
Polarized to Mating Part	Yes
Ports	1
Temperature Range - Operating	-40° to +85°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
NSCC Male Housing, Terminal Size 1.50mm, Non-Sealed, 5.0mm Pitch, 10 Circuits, Black	<u>988231011</u>

Use with Part(s)

Description	Part Number
NSCC Receptacle Terminals Size 1.5	<u>98897</u>

Application Tooling

Global

Description	Part Number
Extractor Tool for NSCC Female Housing	<u>638137500</u>