

TECHNICAL SPECIFICATION



MARTCARE® M Series

MARTCARE® M Series Moulded Disposable Mask - Box of 10 - M32 - FFP3V / BEH130-002-A00



DESCRIPTION

The Martcare® range offers a cost-effective solution, with a straightforward selection of easy-to-use PPE, subject to the rigorous batch testing and conformity procedures applicable to the entire JSP PPE range.

OPTIONS

MARTCARE® M Series Moulded Disposable Mask - Box of 10 - M22 - FFP2V (BEH120-002-A00)

MARTCARE® M Series Moulded Disposable Mask - Box of 10 - M32 - FFP3V (BEH130-002-A00)

MARTCARE® M Series Moulded Disposable Mask - Box of 20 - M21 - FFP2 (BEG120-002-B00)

MARTCARE® M Series Moulded Disposable Mask - Box of 20 - M31 - FFP3 (BEG130-002-B00)

SAFETY STANDARDS

EN 149



JSP Limited, Worsham Mill, Minster Lovell, Oxford OX29 0TA, England.

Tel: +44 (0)1993 826050 / Fax: +44 (0)1993 824411 / Email: sales@jspsafety.com / Web: www.jspsafety.com

Do Not Publish without written permission from JSP Limited. Contact copyright@jspsafety.com. Information correct in the United Kingdom at date of issue and may be subject to change. Any third-party machine and automated translations processed by users may have inaccuracies and should not be relied upon.

Page 1 of 2 / Issued 26 Mar 2025 / Copyright 2018 - 2025. JSP Limited. All Rights Reserved.



SPECIFICATIONS

Classification
FFP3 (Filtering Facepiece Particulate, Valved)

Usage
NR (Non-Reusable)



Activated Carbon Layer
No

Maximum Total Inward Leakage (TIL)
2%

UK Assigned Protection Factor
20



Exhalation Valve
Yes - Polystyrene exhalation valve with rubber diaphragm

Mask Material
Polypropylene



Product Weight
16g (Approx)



Filter Type
P (Protects Against Solid and Liquid Aerosols)



(D) Resistance to dust clogging
Yes - D marking = passes optional clogging test

Minimum Filtration Efficiency
99% For FFP3 Rated

Nominal Protection Factor
50


Mask Design
Moulded



Nose Bridge
Moulded in mask


Filter Shelf Life
5 Years

FEATURES




Inner Foam Nose Bridge

Foam padding around the nose area of the mask provides comfort and a firmer fit.



Exhalation Valve

Low resistance exhalation valve for easy breathing.



Metal Free Straps

Mask straps ultrasonically welded ensuring no metal parts in contact with the face.

RANGE



DOWNLOADS



[Image Pack \(ZIP\)](#)



[doc-disposable-dust-masks-martcare-m-series-m32.pdf \(PDF\)](#)



JSP Limited, Worsham Mill, Minster Lovell, Oxford OX29 0TA, England.

Tel: +44 (0)1993 826050 / Fax: +44 (0)1993 824411 / Email: sales@jspsafety.com / Web: www.jspsafety.com

Do Not Publish without written permission from JSP Limited. Contact copyright@jspsafety.com. Information correct in the United Kingdom at date of issue and may be subject to change. Any third-party machine and automated translations processed by users may have inaccuracies and should not be relied upon.

Page 2 of 2 / Issued 26 Mar 2025 / Copyright 2018 - 2025. JSP Limited. All Rights Reserved.

