



**Part Number :** [330110006](#)  
**Product Description :** MX150 Male Terminal for  
Mat-Sealed or Unsealed Connectors, Gold Plating, 22  
AWG, Left Reel Payoff  
**Series Number :** 33011  
**Status :** Active  
**Product Category :** Crimp Terminals



## Documents & Resources

### Drawings


[330110006 sd.pdf](#)  
[313025040-000.pdf](#)

### Specifications

[AS-33000-001-001.pdf](#)  
[AS-33000-001-FR-001.pdf](#)  
[AS-33000-001-001.pdf](#)  
[PS-33012-002-001.pdf](#)  
[TS-33000-001-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Duty-To-Declare
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Crimp Terminals
Series	33011
Description	MX150 Male Terminal for Mat-Sealed or Unsealed Connectors, Gold Plating, 22 AWG, Left Reel Payoff
Application	Power, Wire-to-Board, Wire-to-Wire, Automotive
Comments	Left Reel Payoff
Product Name	MX150
UPC	800756103563

### Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC

### Physical

Gender	Male
Grip Code	22
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin

Net Weight	0.377/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.65mm max.
Wire Size (AWG)	22
Wire Size mm <sup>2</sup>	0.50

## Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

## Mates With / Use With

### Use with Part(s)

Description	Part Number
MX150 Mat-Sealed Single Row Male Connector Assemblies	<a href="#"><u>33481</u></a>
MX150 Mat-Sealed Dual Row Male Connector Assemblies	<a href="#"><u>33482</u></a>

---

## Application Tooling

### Global

Description	Part Number
Extraction Toolkit for MX150 Connectors	<a href="#"><u>2002220700</u></a>
PremiumGrade Hand Crimp Tool for 1.50mm MX150 Blade Male Terminals, 22-18 AWG	<a href="#"><u>638112600</u></a>
Extraction Tool for MX150L, MX150, PT Bulb Socket, iGrid, SPOX, and Wire-to-Motor Terminals	<a href="#"><u>638131500</u></a>
FineAdjust Applicator for MX150 Male Terminals, 22 AWG and 0.50mm <sup>2</sup> wire	<a href="#"><u>639000600</u></a>

FineAdjust Applicator for SRC Connector using MX150 (M3) Blade Terminals, 0.50mm <sup>2</sup> CHEMINAX 2021D0309 wire	<u>639042100</u>
--	------------------

---

This document was generated on Aug 04, 2025