

## Features

- Protection Class IP54

## RS PRO General Purpose Enclosures

RS Stock No.: 0794444



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## General Specifications

|                 |                                                                                       |
|-----------------|---------------------------------------------------------------------------------------|
| Use             | Machined surfaces and versatile mounting options for connectors, switches and buttons |
| Body Material   | ABS                                                                                   |
| Colour          | Black                                                                                 |
| Lid Colour      | Black                                                                                 |
| Handheld        | No                                                                                    |
| Explosion Proof | No                                                                                    |
| Flanged         | Yes                                                                                   |
| Weight          | 0.015kg                                                                               |
| RAL Code        | RAL 9005                                                                              |

## Mechanical Specifications

|                 |         |
|-----------------|---------|
| Gasket Material | CR Lose |
| External Height | 21mm    |
| External Length | 70mm    |
| External Width  | 40mm    |

## Protection Category

|           |      |
|-----------|------|
| IP Rating | IP54 |
|-----------|------|

## Similar Products

| Stock No. | Brand  | Colour                                    | Shielded | External Dimensions<br>L x W x H | Flanged | Weight  |
|-----------|--------|-------------------------------------------|----------|----------------------------------|---------|---------|
| 0794425   | RS PRO | Light Grey /<br>Lid Colour:<br>Light Grey | No       | 105 x 70 x<br>40mm               | Yes     | 0.123kg |
| 0794427   | RS PRO | Light Grey /<br>Lid Colour:<br>Light Grey | No       | 150 x 100 x<br>45mm              | Yes     | 0.215kg |
| 0794428   | RS PRO | Light Grey /<br>Lid Colour:<br>Light Grey | No       | 97 x 60 x 19mm                   | No      | 0.243kg |
| 0794454   | RS PRO | Light Grey /<br>Lid Colour:<br>Light Grey | No       | 142 x 69 x<br>25mm               | No      | 0.107kg |
| 0794463   | RS PRO | Light Grey /<br>Lid Colour:<br>Light Grey | No       | 90 x 60 x 40mm                   | Yes     | 0.098kg |
| 0794467   | RS PRO | Light Grey /<br>Lid Colour:<br>Light Grey | No       | 45 x 45 x 40mm                   | Yes     | 0.049kg |
| 0794476   | RS PRO | Light Grey /<br>Lid Colour:<br>Light Grey | No       | 70 x 50 x 37mm                   | No      | 0.091kg |
| 0794477   | RS PRO | Light Grey /<br>Lid Colour:<br>Light Grey | No       | 89 x 75 x 41mm                   | No      | 0.091kg |
| 0794478   | RS PRO | Light Grey /<br>Lid Colour:<br>Light Grey | No       | 89 x 75 x 41mm                   | No      | 0.001kg |
| 0794482   | RS PRO | Light Grey /<br>Lid Colour:<br>Light Grey | No       | 51 x 49 x 36mm                   | No      | 0.001kg |
| 0794433   | RS PRO | Light Grey /<br>Lid Colour:<br>Light Grey | No       | 283 x 193 x<br>96mm              | No      | 0.001kg |
| 0794434   | RS PRO | Light Grey /<br>Lid Colour:<br>Light Grey | No       | 70 x 50 x 37mm                   | No      | 0.001kg |
| 0794435   | RS PRO | Light Grey /<br>Lid Colour:<br>Light Grey | No       | 177 x 126 x<br>56mm              | No      | 0.001kg |

## Similar Products CONT

| Stock No. | Brand  | Colour                                    | Shielded | External Dimensions<br>L x W x H | Flanged | Weight  |
|-----------|--------|-------------------------------------------|----------|----------------------------------|---------|---------|
| 0794436   | RS PRO | Light Grey /<br>Lid Colour:<br>Light Grey | No       | 225 x 175 x<br>80mm              | No      | 0.001kg |
| 0794437   | RS PRO | Light Grey /<br>Lid Colour:<br>Light Grey | No       | 210 x 140 x<br>60mm              | No      | 0.354kg |
| 0794442   | RS PRO | Light Grey /<br>Lid Colour:<br>Light Grey | No       | 51 x 49 x 36mm                   | No      | 0.034kg |
| 0794443   | RS PRO | Light Grey /<br>Lid Colour:<br>Light Grey | No       | 177 x 125 x<br>56mm              | No      | 0.282kg |
| 0794444   | RS PRO | Black / Lid<br>Colour: Black              | No       | 70 x 40 x 21mm                   | Yes     | 0.015kg |
| 0794445   | RS PRO | Black / Lid<br>Colour: Black              | No       | 145 x 74 x<br>40mm               | Yes     | 0.103kg |
| 0794447   | RS PRO | Black / Lid<br>Colour: Black              | No       | 155 x 49 x<br>27mm               | Yes     | 0.064kg |
| 0794449   | RS PRO | Light Grey /<br>Lid Colour:<br>Light Grey | No       | 63 x 57 x 37mm                   | No      | 0.001kg |
| 0794451   | RS PRO | Light Grey /<br>Lid Colour:<br>Light Grey | No       | 225 x 175 x<br>80mm              | No      | 0.512kg |