




EN ISO 20345:2011



RESOLUTE TEMPRA 43461-02L

S3 SRC *CI AVAILABLE
Size: 36-48
Weight: 600 gr.

Fit: 11

Working Environment:
 Multipurpose, Logistics and Light Industry, Components and Automotive, ESD Areas


FEATURES

UPPER

 MicroFiber Suede 1,8-2,0 mm
 Reflex insert
 Recycled Digitex Hydro Airy

LINING

3D Green Air 320 gr.

ANTISLIP LINING

DUALMICRO

INSOLE

QRS02 Green

TOE CAP

Fiber cap SXT

RESISTANCE TO PERFORATION

KX Antiperforation recycled PS

TYPE

Low Shoe

SOLE

PU / PU ESD-PLUS SRC

Double density PU sole, Outer- and in-between sole with ESD compound. For use in contact with sensitive electronic equipment. Light and comfortable, very versatile, highly non-slip SRC Antislip standard.

TECHNOLOGIES

Removable Insole



Anatomical breathable insole. Resistant fabric with recycled open-cell foam that absorbs shocks and reduces fatigue. Eliminates sweat with its high ability to evaporate it. Continuous comfort for months and months of use



Protection elements


 RESISTANT
TO 3.0 mm.
NAILS

fibercap sxt

Composite toecap with fiberglass. Resistant to over 200J. Recycled non metal perforation resistant insert to over 1100 N with a 3.0 mm truncated cone nail. Protection over the entire sole of the foot. Flexible and comfortable



Lateral stability

 dynamic **HC** control
technology

Ergonomic rigid internal structure. It houses the heel into the right seat, adjusting the foot support and control of the ankle sideways movements. It keeps the foot tight to the shoe, allowing the perfect fit.



Torsional stability


STABIL•ACTIVE

Support made of rigid plastic material. It supports the heel bone, the instep and tarsal joints, without altering energy absorption. A support for the natural movement of the foot; it provides comfort and greater stability.



Electrical features



ESD footwear discharge static electricity and avoid damaging surrounding objects; they are designed in compliance with the following standards: IEC EN 61340-5-1:2016 - IEC EN 61340-4-3:2018 - IEC EN 61340-4-5:2018.

Other


**GREEN
SOLUTION**

The green proposal by SIXTON PEAK®. RESOLUTE GREEN contains over 40% of GRS certified recycled products with pre and post-consumer origins (ratio calculated on the surface of the upper)



SRC (SRA+SRB)


 SOLE 43
PU - PU

SRA CERAMIC + DETERGENT SOLUTION	FLAT ≥0.32 HEEL (CONTACT ANGLE °°) ≥0.28	0.39
SRB STEEL + GLYCEROL	FLAT ≥0.18 HEEL (CONTACT ANGLE °°) ≥0.13	0.24

EN ISO 20344:2011