

# Pilot devices - Compact range


## Two and three position selector switches, non-illuminated



### Contacts actuated

#### Two position selector switch

Contacts included,




	11	13	21	23
1NO	-	1	-	-
2NO	-	1	-	1
1NC	1	-	-	-
2NC	1	-	1	-
1NO + 1NC	-	1	1	-



### Contacts actuated

#### Three position selector switch

Contacts included,



	21	23	11	13
2NO	-	1	-	1
2NC	1	-	1	-
1NO + 1NC	1	-	-	1

### Codes for handles

Type	Order Code
Black <b>B</b>	6
Red <b>R</b>	1
Grey <b>U</b>	7

Description	Type	Order Code	Weight, kg
-------------	------	------------	------------

#### Selector switch with. Short handle.

##### Two positions

##### Maintained

Contacts included:

1 NO		C2SS1-10■-10	1SFA 619 200 R101□	0.020
2 NO		C2SS1-10■-20	1SFA 619 200 R102□	0.024
1 NC		C2SS1-10■-01	1SFA 619 200 R104□	0.020
2 NC		C2SS1-10■-02	1SFA 619 200 R105□	0.024
1 NO + 1 NC		C2SS1-10■-11	1SFA 619 200 R107□	0.024

##### Maintained

Contacts included:

1 NO		C2SS2-10■-10	1SFA 619 201 R101□	0.020
2 NO		C2SS2-10■-20	1SFA 619 201 R102□	0.024
1 NC		C2SS2-10■-01	1SFA 619 201 R104□	0.020
2 NC		C2SS2-10■-02	1SFA 619 201 R105□	0.024
1 NO + 1 NC		C2SS2-10■-11	1SFA 619 201 R107□	0.024

##### Momentary

Contacts included:

1 NO		C2SS3-10■-10	1SFA 619 202 R101□	0.020
2 NO		C2SS3-10■-20	1SFA 619 202 R102□	0.024
1 NC		C2SS3-10■-01	1SFA 619 202 R104□	0.020
2 NC		C2SS3-10■-02	1SFA 619 202 R105□	0.024
1 NO + 1 NC		C2SS3-10■-11	1SFA 619 202 R107□	0.024

#### Selector switch with. Short handle.

##### Three positions

##### Maintained

Contacts included:

2 NO		C3SS1-10■-20	1SFA 619 210 R102□	0.024
2 NC		C3SS1-10■-02	1SFA 619 210 R105□	0.024
1 NO + 1 NC		C3SS1-10■-11	1SFA 619 210 R107□	0.024

##### Momentary

Contacts included:

2 NO		C3SS2-10■-20	1SFA 619 211 R102□	0.024
2 NC		C3SS2-10■-02	1SFA 619 211 R105□	0.024
1 NO + 1 NC		C3SS2-10■-11	1SFA 619 211 R107□	0.024

##### Momentary

Contacts included:

2 NO		C3SS3-10■-20	1SFA 619 212 R102□	0.024
2 NC		C3SS3-10■-02	1SFA 619 212 R105□	0.024
1 NO + 1 NC		C3SS3-10■-11	1SFA 619 212 R107□	0.024

##### Momentary


Contacts included:

2 NO		C3SS7-10■-20	1SFA 619 216 R102□	0.024
2 NC		C3SS7-10■-02	1SFA 619 216 R105□	0.024
1 NO + 1 NC		C3SS7-10■-11	1SFA 619 216 R107□	0.024

### Ordering example – Compact selector switches

Requested: A red compact selector switch with three positions, Momentary, spring return from A to B and maintained position in C. With 2 NC contacts.

Order: 10 pieces of C3SS7-10R-02



Minimum order quantity: 10 pieces  
Packing: 10 pieces/plastic bag,  
10 bags/box