

HS LC-H-D2SP/ R1XC3 - Fiber optic

1474390

<https://www.phoenixcontact.com/gb/products/1474390>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Multiple light guides, passive, rigid, Raised head, emission surface: spherical, number of displays: 3, (1 row, 3 columns), pitch: 2.54 mm, ESD protection: <8 kV, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed)

Your advantages

- Light guides are perfectly matched to electronics housings
- Easy mounting on the PCB using press pins
- Resistance to ESD
- Housing processing available on request
- Enables simple visual status and diagnostic indicators

Commercial data

Item number	1474390
Packing unit	50 pc
Minimum order quantity	1,000 pc
Sales key	ACGABA
Product key	ACGABA
GTIN	4063151888756
Weight per piece (including packing)	0.66 g
Weight per piece (excluding packing)	0.66 g
Customs tariff number	90019000
Country of origin	DE

HS LC-H-D2SP/ R1XC3 - Fiber optic



1474390

<https://www.phoenixcontact.com/gb/products/1474390>

Technical data

Notes

Assembly note	Please observe the application note in the download area.
---------------	---

Product properties

Product type	Fiber optic
Number of positions	3
Pitch	2.54 mm
Number of rows	1
Alignment	Horizontal
Type	passive, rigid
Conductor type	Multiple light guides
Head form	Raised head
Number of indicators	3 (1 row x 3 columns)

Electrical properties

ESD protection	< 8 kV
----------------	--------

Dimensions

Diameter	2 mm
Hole diameter	1.1 mm
Pitch	2.54 mm

Material specifications

Color (Light guide)	transparent
Insulating material	Polycarbonat

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 85 °C

HS LC-H-D2SP/ R1XC3 - Fiber optic



1474390

<https://www.phoenixcontact.com/gb/products/1474390>

Classifications

ECLASS

ECLASS-13.0	27460404
-------------	----------

ETIM

ETIM 9.0	EC002943
----------	----------

HS LC-H-D2SP/ R1XC3 - Fiber optic



1474390

<https://www.phoenixcontact.com/gb/products/1474390>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk