




Products | Custom Design | Media | Optic Types | Where To Buy | Contact Us

 sales@carclo-optics.com

 +44 1753 575 011

 [LinkedIn](#) 

67mm Wide Spot Frosted Silicone (60031)























Part no.	60031
Family	Silicone S1
Type	Silicone
Diameter	67
Beam	Wide Spot
Finish	Frosted



LEDs & Performances

Select LED to view available holders

Manu.	Performance Data	Images	IES/STP	Interconnect
 LUMILEDS LUXEON COB 1203	Eff: 76.5 FWHM: 40 Cd/lm: 1.8	 	View	Philips Fortimo SLM H 1619
 LUMILEDS LUXEON COB 1203	Eff: 74 FWHM: 39 Cd/lm: 1.8	 	View	Molex 180555 1031
	Eff: 43 FWHM: 43		View	Philips Fortimo SLM H

LUMILEDS LUXEON COB 1204	Cd/lm: 86.5		2024 G1
 LUMILEDS LUXEON COB 1204	Eff: 86.5 FWHM: 43 Cd/lm: 1.6	 	View Molex 180555 1041
 LUMILEDS LUXEON COB 1204 HD	Eff: 77.5 FWHM: 40 Cd/lm: 1.8	 	View Philips Fortimo SLM H 1619
 LUMILEDS LUXEON COB 1204 HD	Eff: 82 FWHM: 40 Cd/lm: 1.8	 	View Molex 180555 1031
 LUMILEDS LUXEON COB 1205	Eff: 82.5 FWHM: 44 Cd/lm: 1.5	 	View Molex 180555 1041



[LUMILEDS LUXEON COB
1205](#)

Eff: 82.5
FWHM: 44
Cd/lm: 1.5



[View](#)

Philips Fortimo SLM H
2024 G1



[LUMILEDS LUXEON COB
1208](#)

Eff: 82.5
FWHM: 45
Cd/lm: 1.4



[View](#)

Molex 180555 1041



[LUMILEDS LUXEON COB
1208](#)

Eff: 83
FWHM: 45
Cd/lm: 1.4




[View](#)

Philips Fortimo SLM H
2024 G1



[LUMILEDS LUXEON COB
1211](#)

Eff: 82
FWHM: 50
Cd/lm: 1.1



[View](#)

Philips Fortimo SLM H
2828 G1

Eff: 82




FWHM: 50
Cd/lm: 1



[View](#)

Molex 180555 1051

[LUMILEDS LUXEON COB
1211](#)




Eff: 83
FWHM: 40
Cd/lm: 1.9



[View](#)

Philips Fortimo SLM H
1619

[Nichia L 016 Z](#)




Eff: 81.5
FWHM: 39
Cd/lm: 1.9



[View](#)

Molex 180555 1031

[Nichia L 016 Z](#)




Eff: 84
FWHM: 40
Cd/lm: 1.9



[View](#)

Philips Fortimo SLM H
1619

[Nichia NFCWL 036B White](#)




Eff: 82





FWHM: 39
Cd/lm: 1.9



[View](#)

Molux 180555 1031

[Nichia NFCWL 036B White](#)