

Features

- Precise temperature control
- Auto sleep
- Temperature lock
- °C / °F switch
- Auto standby
- Temperature calibration

RS PRO Soldering Station 60W, 230V, 200-480°C

RS Stock No.: 0631072



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RRS PRO Digital Soldering Station

This soldering station designed for precision, efficiency, and reliability. With a temperature range of 200–480° C, it is suitable for a wide variety of soldering tasks, from electronics repair to DIY projects. With its adjustable temperature range, PID temperature control, and stable performance, it's easy to use and delivers precise results. Engineered for both professionals and hobbyists, this soldering station delivers high-quality performance at a low cost, making it an ideal choice for those who seek affordability without compromising on quality.

Features and Benefits

- Fast heat-up time for quick use.
- PID temperature control for precision temperature regulation.
- Universal soldering iron tips providing flexibility and cost-effectiveness for users who need different tip shapes for various applications.

General Specifications

Plug Type	Type G – British 3-pin; Type E (France-2 round pins + hole for ground)
Tasks Supported	Soldering
Wattage	60 W
Input Voltage	230 V
Soldering Tip Temperature	200–480 °C
Number of Outputs	1
Display Type	No
ESD Safe	No

Approvals

Declarations	REACH DoC
Standards Met	CE, UKCA, RoHS

Similar Products

Stock No.	Brand	Product Name	Wattage	Tasks Support	Plug Type
0631067	RS PRO	Soldering Station	60W	Desoldering / Soldering	Type G & Type E
0631068	RS PRO	Soldering Station	80W	Desoldering / Soldering	Type G & Type E
0631069	RS PRO	Soldering Station	70W	Desoldering / Soldering	Type G & Type E
0631071	RS PRO	Soldering Station	80W	Desoldering / Soldering	Type G & Type E
0631072	RS PRO	Soldering Station	60W	Desoldering / Soldering	Type G & Type E
0631066	RS PRO	Soldering Iron	90W	Desoldering / Soldering	Type G & Type E


Soldering Iron

Stock No.	Brand	Product Name	Power Type	Wattage	Voltage	Temperature Range
0631076	RS PRO	Soldering Iron	Electric	60W	AC 25V (MAX)	200-480 °C

Stock No.	Brand	Product Name	Tip Shape	Tip Size	Tip Angle
2024516	RS PRO	Soldering Tips	Straight Chisel	1.6 mm	0°
2024517	RS PRO	Soldering Tips	Straight Hoof	0.5 mm	45°
2024518	RS PRO	Soldering Tips	Straight Hoof	0.8 mm	45°
2024520	RS PRO	Soldering Tips	Straight Hoof	1 mm	60°
2024521	RS PRO	Soldering Tips	Straight Conical	0.2 mm	0°
2024522	RS PRO	Soldering Tips	Straight Conical	0.2 mm	0°
2024523	RS PRO	Soldering Tips	Straight Conical	0.5 mm	0°
2024524	RS PRO	Soldering Tips	Straight Knife	2 mm	45°
2024526	RS PRO	Soldering Tips	Straight Knife	1.6 mm	45°
2024527	RS PRO	Soldering Tips	Straight Conical	0.2 mm	0°
2024528	RS PRO	Soldering Tips	Straight Hoof	3 mm	45°
2024529	RS PRO	Soldering Tips	Straight Hoof	4 mm	45°
2024530	RS PRO	Soldering Tips	Bent Conical	0.2 mm	153°
2024532	RS PRO	Soldering Tips	Straight Knife	2 mm	45°
2024533	RS PRO	Soldering Tips	Bent Conical	0.5 mm	153°
7998973	RS PRO	Soldering Tips	Conical Chisel	2.4 mm	
7998976	RS PRO	Soldering Tips	Conical Sharp	0.2 mm	
7998979	RS PRO	Soldering Tips	Conical Chisel	1.2 mm	
7998982	RS PRO	Soldering Tips	Conical Chisel	3.2 mm	
7998985	RS PRO	Soldering Tips	Straight Conical	0.8 mm	
7998989	RS PRO	Soldering Tips	Conical Bevel	2 mm	45°

Accessory



Stock No.	Brand	Product Name	Material	For Use With
136-8299	RS PRO	Solder Tip Cleaner kit	Plastic holder with brass wool	Gentle Fine Clean of Soldering Tip
136-8300	RS PRO	Brass Wool for solder Tip Clean	Brass Wool	Gentle Fine Clean of Soldering Tip (1368299, 0631071, 0631069, 0631068)
0631073	RS PRO	Soldering Iron Cleaning Sponge (PK of 5)	N/A	0631068, 0631067, 0631072



Main unit



Soldering Iron



Iron stand

Sponge