



Oil



Heavy Duty

Robust industrial gloves, ensuring superb mechanical protection for heavy-duty applications

- **Advanced durability and protection:** ActivArm® Hycron 27-600 industrial gloves feature a unique, highly durable nitrile formulation, granting users advanced protection against abrasive materials, as well as flexibility and grease and oil resistance
- **Increased comfort:** These grease-resistant gloves are also made from cotton jersey fabric, cushioning the hand and absorbing perspiration
- **Reduced surface defect risks:** Silicone-free by design, ActivArm® Hycron 27-600 work gloves prevent contaminant transfer to metal before painting, resulting in a high-quality finish



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication

Applications

- Handling metal sheets & panels
- Metalworking & assembly operations
- Press injection molding
- Seizing and finishing structural parts
- Fixing, clipping parts and wire harnesses; connecting devices
- Assembly & inspection of components

Key Features

- Tough, durable nitrile formulation*: Oil and abrasion resistance
 - Cotton jersey fabric: For heavy-duty gloves offering optimal comfort
 - Silicone-free design: Clean surfaces for metals and motor manufacture
- *3x greater durability than standard heavy-duty leather alternatives

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024




EN388: 2016

4121B



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm® Hycron® 27-600	Finishing: ¾ Coated Coating Material: Nitrile Liner Material: Cotton Jersey Cuff Style: Knitwrist		8, 9, 10, 11	246-272 mm, 9.68-10.7 inches	Blue	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

