



**Part Number :** [1301530126](#)  
**Product Description :** Super-Safeway In-Line Industrial GFCI, IP69K, Portable, Single Phase, Manual Reset, NEMA 5-20 Watertite Plug and Receptacle, 20A, 120V, 0.61m (2.0') Cord Length  
**Series Number :** 130153  
**Status :** Active  
**Product Category :** Power Distribution  
**Engineering Number :** 20052-1M



Documents & Resources

Drawings  
[1301530126\\_sd.pdf](#)

Product Environment Compliance

Compliance

|                    |                                               |
|--------------------|-----------------------------------------------|
| GADSL/IMDS         | Not Relevant                                  |
| China RoHS         | Not Reviewed per SJ/T 11365-2006              |
| EU ELV             | Not Relevant                                  |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21               |
| REACH SVHC         | Not Reviewed per D(2024)6225-DC (07 Nov 2024) |
| EU RoHS            | Compliant with Exemption 6(c) per EU 2015/863 |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Part Details

### General

|                    |                                                                                                                                                                  |
|--------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Status             | Active                                                                                                                                                           |
| Category           | Power Distribution                                                                                                                                               |
| Series             | 130153                                                                                                                                                           |
| Description        | Super-Safeway In-Line Industrial GFCI, IP69K, Portable, Single Phase, Manual Reset, NEMA 5-20 Watertite Plug and Receptacle, 20A, 120V, 0.61m (2.0') Cord Length |
| Enclosure Rating   | NEMA 4X                                                                                                                                                          |
| NEMA Configuration | NEMA 5-20                                                                                                                                                        |
| Product Name       | Super-Safeway                                                                                                                                                    |
| Type               | GFCI Industrial Duty, Single Phase                                                                                                                               |
| UPC                | 78678889737                                                                                                                                                      |

### Agency

|    |        |
|----|--------|
| UL | E66308 |
|----|--------|

### Electrical

|                               |             |
|-------------------------------|-------------|
| Current - Maximum per Contact | 20.0A       |
| GFCI                          | Yes-In-line |
| GFCI Reset                    | Manual      |
| Ground Continuity Monitor     | No          |
| Open Neutral Relay            | Yes         |
| Voltage - Maximum             | 120V        |

### Physical

|                     |                         |
|---------------------|-------------------------|
| Cord Diameter       | 10.67mm (.420")         |
| Cord Grip Body Size | Internal Double C-Clamp |
| Cord Length         | 0.61m (2.0')            |
| Cord Type           | 12/3 SJEOOW             |
| Feed-Thru           | Yes                     |
| Flip Lid            | No                      |

|                       |             |
|-----------------------|-------------|
| Material - Housing    | Nylon       |
| Mounting Style        | Portable    |
| Net Weight            | 910.359/g   |
| Number of Receptacles | 1           |
| Packaging Type        | Bag         |
| Receptacle Type       | GFCI Single |

---

This document was generated on Mar 27, 2025