



129-58-4
Socket Set 1/4" & 1/2" 58 Pcs



PRODUCT DETAILS

- 58 pcs socket set
- Hex sockets, metric sizes
- Chrome vanadium alloy steel
- Chrome plated bright finish
- High density polyethylene box
- Box with metal latches
- Standards: DIN 3120, DIN 3124, DIN 3122



PRODUCT ATTRIBUTES

Product			
129-58-4	58	80 x 280 x 380 mm	4750 g

SET CONTENT



Hex Key Nickel Plated 1.5 mm
040001



Hex Key Nickel Plated 2 mm - 5/64"
040011



Hex Key Nickel Plated 2.5 mm
040021



Socket 1/4" Hex 4 mm
101-04-1



Socket 1/4" Hex 4.5 mm
101-045-1



Socket 1/4" Hex 5 mm
101-05-1



Socket 1/4" Hex 5.5 mm
101-055-1



Socket 1/4" Hex 6 mm
101-06-1



Socket 1/4" Hex 7 mm
101-07-1



Socket 1/4" Hex 8 mm
101-08-1



Socket 1/4" Hex 9 mm
101-09-1



Socket 1/4" Hex 10 mm
101-10-1



Socket 1/4" Hex 11 mm
101-11-1



Socket 1/4" Hex 12 mm
101-12-1



Socket 1/4" Hex 13 mm
101-13-1



Extension 1/4" 50 mm
105-22-1



Extension 1/4" 100 mm
105-24-1



Universal Joint 1/4"
105-40-1



Sliding T-Handle 1/4"
105-42-1



Bit Holder Square 1/4" with Hex 1/4"
105-48-1



Spinner Handle 1/4"
105-50-1



Ratchet 1/4" Pear Type, 72 Teeth,
150 mm
105-70-1



Extension 1/2" 125 mm
125-23-1



Extension 1/2" 250 mm
125-25-1



Universal Joint 1/2"
125-40-1



Sliding T-Handle Head 1/2"
125-43-1



Ratchet 1/2" Pear Type, 72 Teeth,
250 mm
125-70-1



1/4" Bit Hex 3, 25 mm, Box 5 Pcs
475-H3-1



1/4" Bit Hex 4, 25 mm, Box 5 Pcs
475-H4-1



1/4" Bit Hex 5, 25 mm, Box 5 Pcs
475-H5-1



1/4" Bit Hex 6, 25 mm, Box 5 Pcs
475-H6-1



1/4" Bit PH1, 25 mm, Box 10 Pcs
475-PH1-1



1/4" Bit PH2, 25 mm, Box 10 Pcs
475-PH2-1



1/4" Bit PH3, 25 mm, Box 10 Pcs
475-PH3-1



1/4" Bit PZ1, 25 mm, Box 10 Pcs
475-PZ1-1



1/4" Bit PZ2, 25 mm, Box 10 Pcs
475-PZ2-1



1/4" Bit PZ3, 25 mm, Box 10 Pcs
475-PZ3-1



1/4" Bit Slotted 4.0, 25 mm, Box 10 Pcs
475-4-1



1/4" Bit Slotted 5, 25 mm, Box 10 Pcs
475-5.5-1



Socket 1/2" Hex 8 mm
121-08-1



Socket 1/2" Hex 10 mm
121-10-1



Socket 1/2" Hex 12 mm
121-12-1



Socket 1/2" Hex 13 mm
121-13-1



Socket 1/2" Hex 14 mm
121-14-1



Socket 1/2" Hex 16 mm
121-16-1



Socket 1/2" Hex 17 mm
121-17-1



Socket 1/2" Hex 19 mm
121-19-1



Socket 1/2" Hex 21 mm
121-21-1



Socket 1/2" Hex 23 mm
121-23-1



Socket 1/2" Hex 26 mm
121-26-1



Socket 1/2" Hex 28 mm
121-28-1



Socket 1/2" Hex 32 mm
121-32-1



Socket 1/2" Hex 20 mm
121-20-1



Socket 1/2" Hex 22 mm
121-22-1



Socket 1/2" Hex 24 mm
121-24-1



Socket 1/2" Hex 27 mm
121-27-1



Socket 1/2" Hex 30 mm
121-30-1