

CV 38/2 ADV GB

With a quick-change system for the Glideflex power cable and integrated accessory holder: the easy-to-use, powerful CV 38/2 Adv carpet vacuum for high area performances.



Order no. **1.033-337.0**

Technical data

EAN code		4054278494470
Current type	V / Hz	220 - 240 / 50 - 60
Working width	cm	38
Vacuum	mbar / kPa	200 / 20
Air flow	l/s	40
Rated performance	W	850
Container content	l	5.5
Standard nominal width		ID 35
Cable length	m	12
Sound pressure level	dB(A)	65
Motor rating of brush motor	W	150
Colour		anthracite
Weight without accessories	kg	8.8
Weight incl. packaging	kg	12
Dimensions (L × W × H)	mm	370 × 390 × 1215

Equipment

Crevice nozzle		■
Upholstery nozzle		■
Detachable suction tube		■
Corrugated suction hose		■
Quantity of filter bags	Piece(s)	1
Filter bag material		Fleece
Filter status indicator		■
Height-adjustable handle		■
Brush roller standard	Piece(s)	1

■ Included in delivery.



Indicator light

- Visual indication for adjusting the brush roller height.
- Roller brush adjustable to different carpet pile heights.
- Optimised brush roller height adjustment for optimum cleaning results.



Quick-change system for Glideflex power cable

- Particularly flexible, sturdy, long-lasting Glideflex power cable.
- Easy to change and does not require any prior knowledge.
- Saves time and reduces service costs.



Flexible and effective cleaning option

- Easy and quick removal of the stretchable suction hose.
- Effortless removal of blockages if required.

EQUIPMENT FOR CV 38/2 ADV GB 1.033-337.0



		Order no.	Description	
SUCTION NOZZLES				
Crevice nozzles				
Crevice nozzle DN35	1	6.906-240.0	Plastic crevice tool (DN 35) for vacuuming in crevices and corners. Length: 250 mm.	<input checked="" type="checkbox"/>
Upholstery nozzles				
Upholstery nozzle complete NW35	2	6.905-998.3		<input checked="" type="checkbox"/>
SUCTION HOSES				
Suction hoses with cone connection				
Suction hose DN32	3	6.391-934.0		<input checked="" type="checkbox"/>
UPRIGHT BRUSH-TYPE VACUUM CLEANER ACCESSORY				
Roller brush CV 38/1, standard	4	6.906-643.0		<input checked="" type="checkbox"/>
Roller brush CV 38/1 /2, red	5	6.906-644.0	Hard, red bristles (e.g. for needle felt).	<input type="checkbox"/>
Roller brush CV 38, antistatic	6	4.762-487.0	Roller brush for CV 38, antistatic.	<input type="checkbox"/>
FURTHER ACCESSORIES DRY VACUUM CLEANERS				
Set hand nozzle	7	2.889-361.0		<input type="checkbox"/>
FILTER BAGS				
Fleece filter bags (3 ply)				
Fleece filter bags, 10 Piece(s), CV 30/1, CV 38/1, CV 38/2, CV 48/2	8	6.904-305.0	3-ply tear-resistant fleece filter bags, dust class M, standard for CV 30/1 and CV 38/1. Contents: x10.	<input type="checkbox"/>
Paper filter bags				
Paper filter bags, 10 Piece(s), CV 30/1, CV 38/1, CV 38/2, CV 48/2	9	6.904-294.0	Paper filter bags, dust class M suitable for all CV 30/1 and CV 38/1 models. Contents: x10.	<input type="checkbox"/>
FILTER T/ NT				
HEPA filter for dust class H				
Filter complete packaged HEPA	10	2.889-286.0		<input type="checkbox"/>

■ Included in delivery. □ Available accessories.