



Thermal protection

TEMPDEX 720

Temperature below 150°C | Dry environments



CUT PROTECTION
LEVEL B

EN388



4X43B

EN407



X2XXXX

CATEGORY 2



ISO 13997:

7 N

DEXTERITY

EN ISO 21420:
5/5

Dexterity and resistance to cuts for optimised thermal protection

SPECIFIC ADVANTAGES



Cut protection

- Knitted aramide fibres ensures protection from cuts



Thermal protection

- Comfort and insulation of the interior terry-cloth



Durability

- Longer service life: good abrasion resistance



Productivity

- Special nitrile Grip coating facilitates work in moderately oily environments



Skin protection

- Free of harmful substances: DMF Free



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting

INDUSTRIES

- Mechanical industry
- Other industries
- Rubber industry

APPLICATIONS

- Vulcanization, demoulding, forming, etc.
- Working with hot, sharp and oily parts
- Handling of hot piping
- Handling of hot steel after welding
- Handling of moulds in the ceramic industry



Thermal protection

TEMPDEX 720

Temperature below 150°C | Dry environments


LEGENDS

EN388

MECHANICAL HAZARDS



PERFORMANCE LEVELS (X = NOT TESTED)




EN407

THERMAL RISKS (HEAT AND FIRE)



PERFORMANCE LEVELS (X = NOT TESTED)



PRODUCT DETAILS

Interior finish	Knitted thermal protection
Gauge	10
Exterior finish	Dots
Material	Nitrile
Cuff characteristic	Knitted Cuff
Colour.s	Black Orange
European sizes	7 9 11
Surface resistance according to EN1149-1 (Value in palm area at 25% relative humidity)	1.6E+10 Ω
Vertical resistance according to EN1149-2 (Value in palm area at 25% relative humidity)	7.5E+11 Ω

LOGISTIC DETAILS

Packaging	1 pair/bag 72 pairs/carton
-----------	-------------------------------

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/09/19/2717 update 02-16/04/2024
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE

Edit 06/01/2025