

Accessoires – Distribution de potentiel

WQV 2.5



Caractéristiques techniques			
Courant permanent 2 pôles / multipol.	A		
Taille filetage	M 2,5		
Couple de serrage	Nm		
Références			
2 pôles	WQV 2.5/2	50	1053660000
3 pôles	WQV 2.5/3	50	1053760000
4 pôles	WQV 2.5/4	50	1053860000
5 pôles	WQV 2.5/5	10	1053960000
6 pôles	WQV 2.5/6	10	1054060000
7 pôles	WQV 2.5/7	10	1054160000
8 pôles	WQV 2.5/8	10	1054260000
9 pôles	WQV 2.5/9	10	1054360000
10 pôles	WQV 2.5/10	20	1054460000
15 pôles	WQV 2.5/15	10	1059660000
32 pôles	WQV 2.5/32	10	1577600000
pour b.j.			
WDU 1.5 ZZ	WDK 2.5		
WDU 1.5 BLZ	WDK 2.5 V		
WDU 2.5/1.5 ZR	WDK 2.5 DU-PE		
WDU 2.5	WDK 2.5 F		
WDU 2.5 F			

32 / 32		
M 2,5		
0,4 ... 0,7		
Type	Cdt	Référence
pour b.j.		

WQV 4



41 / 41		
M 3		
0,5 ... 0,8		
Type	Cdt	Référence
WQV 4/2	50	1051960000
WQV 4/3	50	1054560000
WQV 4/4	50	1054660000
WQV 4/5	10	1057860000
WQV 4/6	10	1057160000
WQV 4/7	10	1057260000
WQV 4/8	10	1057960000
WQV 4/9	10	1058060000
WQV 4/10	20	1758260000
WQV 4/15	10	1057460000
pour b.j.		
WDU 4		
WDU 4 SL		

WQV 6



57 / 57		
M 3		
0,5 ... 0,8		
Type	Cdt	Référence
WQV 6/2	50	1052360000
WQV 6/3	50	1054760000
WQV 6/4	50	1054860000
WQV 6/5	50	1062660000
WQV 6/6	50	1062670000
WQV 6/7	50	1062680000
WQV 6/10	20	1052260000
pour b.j.		
WDU 6		
WDU 4 SL		

WQV 35N



Caractéristiques techniques			
Courant permanent 2 pôles / multipol.	A		
Taille filetage	M 4		
Couple de serrage	Nm		
Références			
2 pôles	WQV 35N/2	50	1079200000
3 pôles	WQV 35N/3	50	1079300000
4 pôles	WQV 35N/4	50	1079400000
5 pôles			
6 pôles			
7 pôles			
8 pôles			
9 pôles			
10 pôles			
15 pôles			
32 pôles			
pour b.j.			
WDU 35N			

115 / 100		
M 4		
1,2 ... 1,8		
Type	Cdt	Référence
pour b.j.		

WQV 50N


(protection des doigts avec capot WAD)



150 / 150		
M 6		
2,5 ... 4,5		
Type	Cdt	Référence
WQV 50N/2	10	1834060000
WQV 50N/3	10	1834070000
WQV 50N/4	10	1834080000
pour b.j.		
WDU 50N		

WQV 70N

(protection des doigts avec capot WAD)



192 / 192		
M 6		
2,5 ... 4,5		
Type	Cdt	Référence
WQV 70N/2	5	9512240000
WQV 70N/3	5	9512250000
WQV 70N/4	5	9531290000
pour b.j.		
WDU 70N		