

DUSTING TOOLS V-2100

V-2100

Anti Static Set for AIR DUSTER



EAN: 9 00330862100 8

DUSTING TOOLS

extend our range of GREEN-CLEAN aerosols AIR + VACUUM POWER into multifunctional tools. Extremely robust and designed for repeated use on many cans. The improved method is time-saving due to better working advantages, at the same time preventing the use of unnecessary one way part.

Application Advantages ANTI STATIC ADAPTER for TOP Ventil V-2000

- Material Thunderon works by ionising the gas stream
- Works as long as the brush itself stays clean
- No surface contact necessary
- Especially for small components, slides ...
- Removes dust AND static electricity charging



To use with GREEN CLEAN AIR POWER:

G-2016	150 ml / 173 gr	not flammable
G-2041	400 ml / 342 gr	flammable
G-2051	400 ml / 462 gr	not flammable



Technical Details:

Description		Size in cm	Weight	Private Logo	Material:
TOP VENTIL V-2000 with Anti-static brush-adapter		Trigger ø 30 cranked Aluminium Pipe 120 mm	42,2 gr.		Top valve: POM + Aluminium Adapter: Thunderon
Packaging	Units				
Box	4 Units	21,0 x 8,0 x 20,5	273,3 gr.	Shipping	Storage
Box	12 Units	27,0 x 21,5 x 20,7	700,8 gr.	No reg.	No reg.
Pallet / Rows	15 x 12 Units =	180 Units	10,51 kg	Tariff Number	Chem. Reg.
max. Rows :	6 Rows =	1080 Units	63,07 kg	8428995	No reg.

DUSTING TOOLS V-2100

V-2100

Anti Static Set zu AIR DUSTER



EAN: 9 00330862100 8

DUSTING TOOLS erweitern GREEN CLEAN AirDuster zum multifunktionalen Werkzeug zum Ausblasen oder Absaugen, mit **Anti Static Wirkung** oder mit Verlängerungen

Anwendungsvorteile ANTI STATIC ADAPTER - Bürstenadapter zu TOP VENTIL

- entfernt Staub UND statische Aufladung – kontaktlos und rückstandsfrei
- wirkt durch Ionisierung des Gasstromes
- funktioniert, solange die Bürste nicht verschmutzt
- kein Oberflächenkontakt erforderlich



Zu verwenden mit GREEN CLEAN AIR POWER:

G-2016	150 ml / 173 gr	unbrennbar
G-2041	400 ml / 342 gr	brennbar
G-2051	400 ml / 462 gr	unbrennbar



Technische Beschreibung:

Beschreibung		Maße in cm	Gewicht	Private Logo	Material:
TOP VENTIL V-2000 mit Anti Static Bürstenadapter		Drücker ø 30 Alu Rohr gekröpft 120 mm	42,2 gr.		Top Ventil: POM Alu-Adapter: Thunderon
Verpackung	Stück				
Kreuzhülle	4 Stk.	21,0 x 8,0 x 20,5	273,3 gr.	Versand	Lagerung
Karton	12 Stk.	27,0 x 21,5 x 20,7	700,8 gr.	keine Vo	keine Vo
Palette je Reihe	15 x 12 Stk = 180 Stk.		10,51 kg	ZollPosnr.	ChemVo
max. Reihen :	6 Reihen = 1080 Stk.		63,07 kg	8428995	keine Vo