


SD5920T EQ Thunderbolt™ 4 Quad 4K Hybrid Dock with DisplayLink® Technology



Supporting up to four external displays on laptops running Windows, macOS and ChromeOS, the SD5920T EQ Thunderbolt™ 4 Quad 4K Hybrid Dock with DisplayLink® Technology is a versatile docking station for unlocking the full potential of Thunderbolt™ 4, Thunderbolt™ 3, USB4® and USB-C® devices. Flexible video connections include 2 x HDMI®/DP ports, 1 x DP port and 1 x Thunderbolt™ 4 port, supporting up to Quad 4K @ 60Hz. Focused on productivity, the SD5920T supports up to 100W Charging (96W certified) to the laptop, 40Gbps data transfer speeds and includes 16 connectivity ports. Partially made with recycled materials. Includes security cable lock slots and 3-year limited warranty. * For MacBook M1/M2/M3/M4 with Pro and Max chipsets (and M3 base chipset when laptop lid is closed), this dock supports up to quad 4K @ 60Hz. It also supports up to triple 4K @ 60Hz for M1/M2 base chipsets.



Attributes

- Supports up to Quad 4K @ 60Hz for Thunderbolt™ 4 laptops and devices via plug-and-play TB4 port and MacBook* models with M1/M2/M3 Pro and Max chipsets via DisplayLink®. * For MacBook M1/M2/M3/M4 with Pro and Max chipsets (and M3 base chipset when laptop lid is closed), this dock supports up to quad 4K @ 60Hz. It also supports up to triple 4K @ 60Hz for M1/M2 base chipsets.
- Optimised for Thunderbolt™ 4, Thunderbolt™ 3, USB4® and USB-C® devices running Windows (10 or later), macOS (11 or later) and ChromeOS (116 or later).
- Composed of 100% post-consumer recycled (PCR) aluminium* and delivered in FSC® certified packaging. * The outer casing of the docking station is made of aluminium. The PCBA and any related inner components are not made of aluminium.
- Combines Thunderbolt™ with DisplayLink® to provide next-level productivity experiences, including up to 40Gbps of data, video and audio, daisy chain support, together with Intel VT-d DMA protection.
- Up to 100W Charging (96W certified) to power your laptop and connected accessories.
- Productive 16-in-1 design allows users to work more efficiently and connect to a variety of setups.
- Zero-footprint mounting option support a tidier workspace.
- Security cable lock slots support device protection.
- 3-Year limited warranty.

Specifications

Number	K35234EU
Colour	-----
Dimensions (W x H x D)	85 x 22 x 225 mm
Weight	605 g
Pallet quantity	216
EAN code	5028252650861