



Main

Range	PrismaSeT
Product or component type	Door
Accessory / separate part category	Enclosure accessory
Range compatibility	PrismaSeT XS

Complementary

Enclosure mounting	Flush Surface
Key number	Number to be stated
Door type	Plain
Door opening side	Right or left
Number of horizontal rows	1
9 mm pitches	48.0
Number of 18 mm modules per row	24
Total number of 18 mm modules	24.0
Net weight	2.960 Kg
Enclosure material	Steel
Width	550 Mm
Height	300 Mm
Depth	20 Mm
Colour	White (RAL 9003)
Market segment	Residential Small buildings

Environment

IP degree of protection	IP40
IK degree of protection	IK09
Ambient air temperature for operation	-25...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.200 Cm
Package 1 Width	39.000 Cm
Package 1 Length	63.500 Cm
Package 1 Weight	2.500 Kg
Unit Type of Package 2	P12
Number of Units in Package 2	43
Package 2 Height	117.000 Cm
Package 2 Width	80.000 Cm
Package 2 Length	120.000 Cm
Package 2 Weight	124.000 Kg

Offer Sustainability

Total lifecycle Carbon footprint	17 kg CO2 eq.
Carbon footprint of the manufacturing-phase [A1 to A3]	12.478419185493335
Carbon footprint of the manufacturing-phase [A1 to A3]	12 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.16642958361941634
Carbon footprint of the distribution phase [A4]	0.2 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.03165218983760655
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0
REACH free of SVHC	Yes
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Carbon footprint of the end-of-life phase [C1 to C4]	4.242157640708792
Carbon footprint of the end-of-life phase [C1 to C4]	4 kg CO2 eq.
Environmental Disclosure	 Product Environmental Profile
Total lifecycle Carbon footprint	17
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
REACH Regulation	 REACH Declaration
REACH Regulation	Free of Substances of Very High Concern above the threshold
EU RoHS Directive	Compliant
Halogen-free status	Product contains halogen above thresholds
End of life manual availability	No need of specific recycling operations