


Product data sheet

Specifications



Terminal block kit, Linergy, 8 holes,
4x16 mm² + 4x10 mm², for earth or
neutral connection

LGYT2A08

Main

Range	Linery
Product or component type	Terminal block kit
Accessory / separate part category	Connection accessory Spare part
Range compatibility	PrismaSeT XS Mureva enclosure Easy9 EU Resi9 MP
Colour	Cover: green Cover: blue

Complementary

Product destination	PrismaSeT XS enclosure 13 modules PrismaSeT XS enclosure 18 modules Mureva Enclosure enclosure Easy9 EU enclosure Resi9 MP enclosure
Mounting support	Chassis DIN rail
Provided equipment	1 x terminal 1 x terminal block support 2 x cover
Enclosure mounting	Flush Surface
[In] rated current	80 A
[Ue] rated operational voltage	440 V AC
[Ui] rated insulation voltage	750 V
Number of terminal blocks	1 earth / neutral (screw terminal) with 8 outgoers
Distribution block outgoers	4 x 16 mm ² for earth / neutral 4 x 10 mm ² for earth / neutral
Connections - terminals	Screw terminals (earth / neutral) , 4 x 10 mm ² (flexible) Screw terminals (earth / neutral) 16 mm ² (rigid) Screw terminals (earth / neutral) 16 mm ² (stranded) Screw terminals (earth / neutral) 10 mm ² (flexible with ferrule)
Material	Cover: plastic Terminal: brass

Environment

Ambient air temperature for storage	-25...60 °C
-------------------------------------	-------------

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.600 cm
Package 1 Width	5.000 cm
Package 1 Length	8.000 cm
Package 1 Weight	46.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	70
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.832 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	2f760a08-b7ef-4260-b7b6-69e4399d3265
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
PVC free	Yes

Use Longer

Lifetime extension	
Repair	No

Use Again

Repack and remanufacture	
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative



