

CORD CONNECTOR:

NEMA CONFIGURATION

Cat. No	Config	Cord AWG	Electrical A/V	Sec.	FIG.	C-UL
WS-022	5-15	16,14/3	13,15/125	2	3	Yes
WS-022(A.C.1)	5-15	14,12/3	15/125	2	3B	Yes
WS-022-5	5-15	18, 16, 14/3	10, 13, 15/125V	2	3A	Yes
WS-108	L5-15	14,12,10/3	15,15,15/125	2	22	Yes
WS-109	1-15	16/2	13/125	2	17	Yes
WS-111	L5-20	14,12,10/3	18,20,20/125	2	23	Yes
WS-111-2	L5-20	12, 10	20, 20/125	2		Yes
WS-113	L5-30	14,12,10/3	18,25,30/125	2	24	Yes
WS-113-2	L5-30	12, 10	25, 30/125	2		Yes
WS-116-3	5-15	18,16,14,12/3	10,13,15,15/125	2	16	Yes
WS-116-5	5-15	18,16,14,12/3	10,13,15,15/125	2	31,32	Yes
WS-170	5-20	16,14,12/3	13,15,20/250	2	10	Yes
WS-170-1	5-20	16,14,12/3	13,15,20/125	2	11	Yes
WS-171	6-20	16,14,12/3	13,15,20/125	2	-	Yes
WS-172	6-15	16,14,12/3	13,15,15/250	2	-	Yes
WS-173	L6-15	14,12,10/3	15,15,15/250	2	25	Yes
WS-174	L6-20	14,12,10/3	18, 20, 20/250	2	18	Yes
WS-174-2	L6-20	12, 10	20, 20/250	2		Yes
WS-175	L6-30	14,12,10/3	18, 25, 30/250	2	19	Yes
WS-175-2	L6-30	12, 10	25, 30/250	2		Yes
WS-176	L14-20	14,12,10/4	15,20,20/125,250	2	20	Yes
WS-176-2	L14-20	12, 10	20, 20/125,250	2		Yes
WS-177	L14-30	14,12,10/4	15,20,30/125,250	2	21	Yes
WS-177-2	L14-30	12, 10	20, 30/125,250	2		Yes
WS-178	L15-20	14,12,10/4	18,20,20/250	2	26	Yes
WS-178-2	L15-20	12, 10	20, 20/250, 3-PH	2		Yes
WS-179	L15-30	14,12,10/4	18,25,30/250	2	27	Yes
WS-179-2	L15-30	12, 10	25, 30/250, 3-PH	2		Yes
WS-241	5-15	16,14/3	13,15/125	2	12	Yes
WS-026-1	1-15	16,14/2	13,15/125	2	13	Yes
WS-026-3	1-15	16,14/2	13,15/125	2	14	Yes
WS-026-5	1-15	16,14/2	13,15/125	2	15	Yes
WS-026-6	1-15	18, 16, 14/2	10, 13, 15/125	2	15A	Yes

IEC CONFIGURATION

Cat. No.	Config	Cord AWG	A/V	Sec.	FIG.	C-UL
WS-002	C13	18,16,14,12/3	10,13,15,15/125,250	2	1	Yes
WS-002-2	C13	18,16,14,12/3	10,13,15,15/125,250	2	1	No
WS-002A-R	C13	18,16,14/3	10,13,15/125,250	2	1	Yes
WS-002A-L	C13	18,16,14/3	10,13,15/125,250	2	1	Yes
WS-002B	C13	18,16,14/3	10,13,15/125,250	2	1	Yes
WS-002C	C15	18,16,14/3	10,13,15/125,250	2	1	Yes
WS-002C-1	C15	18,16,14/3	10,13,15/125,250	2	-	Yes
WS-002C-2	C15	18,16,14/3	10,13,15/125,250	2	-	Yes
WS-002C-5	C15	18,16,14/3	10,13,15/125,250	2	-	Yes
WS-002C-0	C15	18,16,14/3	10,13,15/125,250	2	1-1	Yes