

ES/KLM 2-GB - Insert strip



0800954
<https://www.phoenixcontact.com/gb/products/0800954>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insert strip, Sheet, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, Office printing systems, perforated, mounting type: insert, Number of individual labels: 120, text field height: 7 mm, text field width: 44 mm



Commercial data

Item number	0800954
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG2114
Product key	BG2114
GTIN	4017918129286
Weight per piece (including packing)	10.215 g
Weight per piece (excluding packing)	9.575 g
Customs tariff number	48025890
Country of origin	DE

Technical data

Notes

General	Print image may vary depending on laser printer
---------	---

Product properties

Product type	Terminal marking
--------------	------------------

Marking

Number of individual labels	120
Number of individual labels per row	4

Dimensions

Width	44 mm
Height	7 mm
Depth	0.2 mm

Text field

Text field width	44 mm
Text field height	7 mm

Material specifications

Color	white (RAL 9010)
Material	Polyester foil
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	insert
---------------	--------

ES/KLM 2-GB - Insert strip



0800954

<https://www.phoenixcontact.com/gb/products/0800954>

Classifications

ECLASS

ECLASS-13.0	27281106
-------------	----------

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

ES/KLM 2-GB - Insert strip



0800954
<https://www.phoenixcontact.com/gb/products/0800954>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk