



Hand protection

# V1600

## DISPOSABLE

Disposable nitrile chemical tactile glove with excellent grip in oily environments thanks to its embossed diamond texture.



### Specific benefits



#### Easy to use

· Touch screen, so you can use your tablet or smartphone without removing your gloves



#### Hygiene

· Nitrile means no risk of allergies for users



#### Performance

· The nitrile coating gives people working in oily/greasy environments an excellent grip on the objects they handle



#### Compatibility

· Ambidextrous glove

### Applications

- Agriculture
- Public works
- Building
- Finishing works / Craftsmanship
- Heavy industry
- Maintenance

### Certifications and norms



EN ISO 374-1  
TYPE B  
JKT



EN ISO 374-5

VIRUS



EN ISO 374-5

### Protects against risks



Biological



Chemical



Particules



Hand protection

# V1600

DISPOSABLE

Disposable nitrile chemical tactile glove with excellent grip in oily environments thanks to its embossed diamond texture.

## Standards - Details



EN 374

J  
K  
T

## Technical details

Glove kind	Tight glove
Glove family	Tight glove unsupported powder free
Tight glove kind	Unsupported
Coating level	Fully coated
Coating material	Nitrile
Coating finition	Grip-textured
Number of layer	Single layer
Inner finition	Powder free
Thickness (mm)	0.17
Arm level protection	Standard cuff (< 290mm)
Benefits element	Touch screen
Color	Black
Size	6, 7, 8, 9, 10
Lifespan from manufacturing (years)	5
Type of packaging	Box of 50



Hand protection

# V1600

## DISPOSABLE

Disposable nitrile chemical tactile glove with excellent grip in oily environments thanks to its embossed diamond texture.

### Permeation table

Chemicals	Letter	CAS #	Permeation level	Permeation time (minutes)	Dégradation moyenne
n-Heptane	J	CAS 142-82-5	4	120	47,5%
Sodium hydroxide 40%	K	CAS 1310-73-2	6	480	-11,1%
Formaldehyde 37%	T	CAS 50-00-0	5	240	36,3%








Safety gloves

# V1600

## DISPOSABLE

Disposable nitrile chemical tactile glove with excellent grip in oily environments thanks to its embossed diamond texture.

### Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
GW1600CZ01BK07 [V1600B5006]	Black	6/7	V1600	3295249305864	13295249305861	10	1	5.0 kg	33.5 cm	27.2 cm	25.4 cm
GW1600CZ01BK08 [V1600B5007]	Black	7/8	V1600	3295249305871	13295249305878	10	1	5.0 kg	33.5 cm	27.2 cm	25.4 cm
GW1600CZ01BK09 [V1600B5008]	Black	8/9	V1600	3295249305888	13295249305885	10	1	5.0 kg	33.5 cm	27.2 cm	25.4 cm
GW1600CZ01BK10 [V1600B5009]	Black	9/10	V1600	3295249305895	13295249305892	10	1	5.0 kg	33.5 cm	27.2 cm	25.4 cm
GW1600CZ01BK11 [V1600B5010]	Black	10/11	V1600	3295249305901	13295249305908	10	1	5.0 kg	33.5 cm	27.2 cm	25.4 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height