

Product Data Sheet

MaxiTherm® 30-201

Colour – Coating	Grey
Colour – Liner	Orange
Design	Palm coated knitwrist
Coating	NRL (Natural Rubber Latex)
Coating texture	Micro-Foam with Non-Slip Grip
Liner	Acrylic, Polyester
Palm thickness	2.50 mm



Dimensions

Size Range	Size 6 (XS)	Size 7 (S)	Size 8 (M)	Size 9 (L)	Size 10 (XL)	Size 11 (XXL)
Total glove length (+/-10 mm)	220	235	245	255	265	275
Wrist length (mm)	70	85	85	90	95	100
Wrist width (mm)	70	75	80	85	90	90
Palm width (+/-3 mm)	100	106	110	114	118	122
Over lock colour	Blue	Red	Orange	White	Yellow	Black

EN test Results

Test	Notified Body	Result/Pass
EN ISO 21420: 2020	TÜV Rheinland	Yes
EN 388: 2016 + A1: 2018	TÜV Rheinland	1241B
EN 407: 2004	TÜV Rheinland	X2XXXX
EN 511: 2006	TÜV Rheinland	X1X



Product Data Sheet

MaxiTherm® 30-201

Typical Performance Values

EN ISO 21420 Dexterity	Level 5
EN 388:2016 + A1:2018 A. Abrasion Resistance	> 100 Cycles
EN 388:2016 + A1:2018 B. Cut Resistance	> 2.5 index
EN 388:2016 + A1:2018 C. Tear Resistance	> 75 newtons
EN 388:2016 + A1:2018 D. Puncture Resistance	> 20 newtons
EN 388:2016 + A1:2018 E. Cut Resistance ISO	≥ 5 Newton

HandCare®

Skin Health Alliance Dermatologically Accredited	Yes
REACH compliant	Yes
Standard 100 by OEKO-TEX® (08.BH.57867)	Certified
Washable	40°
Sanitized®	Yes



Special features

Silicone free	No
---------------	----

Packaging

Pairs per poly bag	12
Poly bags per carton	6
Carton count	72
Carton dimensions (mm)	500 x 295 x 270



Product Data Sheet

MaxiTherm® 30-201

Weight

Size Range	Size 6 (XS)	Size 7 (S)	Size 8 (M)	Size 9 (L)	Size 10 (XL)	Size 11 (XXL)
Glove weight / Pair (+/-6 gram)	96	100	110	118	126	134
Gross Weight (Kg)	8	8.3	9	9.6	10.2	10.8
Carton Weight (Kg)	1	1	1	1	1	1
Net Weight (Kg)	7	7.3	8	8.6	9.2	9.8

Issue date: 29.03.2019

