

### 2160 PZ

#### 3C-SCREWDRIVER for cross-slotted head screws PZ

- ✓ Acc. to DIN ISO 8764, tip acc. to DIN ISO 8764-1 PZ
- ✓ Blade in vanadium plus steel, chrome-plated
- ✓ 3-component handle with hanging hole
- ✓ Size 3 and 4 blade with hexagon bolster



Code	No.	PZ	M	mm	mm	mm	mm	mm	mm	£
6683970	<b>2160 PZ 0</b>	0	M1,6 - M2	3,0	60	140	29	10		
6684000	<b>2160 PZ 1</b>	1	M2 - M3	4,5	80	180	65	10		
6684190	<b>2160 PZ 2</b>	2	M3,5 - M5	6,0	100	210	101	10		
6684270	<b>2160 PZ 3</b>	3	M5,5 - M7	8,0	150	270	13	169	10	
6684350	<b>2160 PZ 4</b>	4	M8 - M10	10,0	200	320	16	253	10	

### 2161 PZ

#### SCREWDRIVER for cross-slotted head screws PZ, stubby

- ✓ Acc. to DIN ISO 8764, tip acc. to DIN ISO 8764-1 PZ
- ✓ Blade in vanadium plus steel, chrome-plated
- ✓ 1-component handle, blue, with hanging hole




Code	No.	PZ	M	mm	mm	mm	mm	mm	£
1550608	<b>2161 PZ 1</b>	1	M2 - M3	4,5	25	75	32	10	
1550616	<b>2161 PZ 2</b>	2	M3,5 - M5	6,0	25	75	37	10	

### 2163 BTX

#### 3C-SCREWDRIVER for recessed TORX® head screws

- ✓ Blade in vanadium plus steel, chrome-plated
- ✓ 3-component handle with hanging hole
- ✓ TORX® = reg. trademark of Acument Intellectual Properties, LLC. USA



Code	No.	BTX	M	mm	mm	mm	mm	mm	mm	£
1828703	<b>2163 BTX T3</b>	T3	M1,2 - M1,4	1.13	3,0	60	140	28	10	
1828711	<b>2163 BTX T4</b>	T4	M1,4	1.29	3,0	60	140	27	10	
1616471	<b>2163 BTX T5</b>	T5	M1,8	1.42	3,0	60	140	28	10	
6685400	<b>2163 BTX T6</b>	T6	M2	1.69	3,0	60	140	29	10	
6685590	<b>2163 BTX T7</b>	T7	M2,5	1.99	3,0	60	140	29	10	
6685670	<b>2163 BTX T8</b>	T8	M2,5	2.31	3,0	60	140	29	10	
6685750	<b>2163 BTX T9</b>	T9	M3	2.50	3,0	60	140	29	10	
6685830	<b>2163 BTX T10</b>	T10	M3 - M3,5	2.74	3,0	80	160	30	10	
6685910	<b>2163 BTX T15</b>	T15	M3,5 - M4	3.27	3,5	80	170	45	10	
6686050	<b>2163 BTX T20</b>	T20	M4 - M5	3.86	4,0	100	190	51	10	
6686130	<b>2163 BTX T25</b>	T25	M4,5 - M5	4.43	4,5	100	200	68	10	
6686210	<b>2163 BTX T27</b>	T27	M4,5 - M6	4.99	5,5	115	215	84	10	
6686480	<b>2163 BTX T30</b>	T30	M6 - M7	5.52	6,0	115	225	105	10	
6686560	<b>2163 BTX T40</b>	T40	M7 - M8	6.65	7,0	130	240	126	10	
6686640	<b>2163 BTX T45</b>	T45	M8 - M10	7.82	8,0	130	250	156	10	
6686720	<b>2163 BTX T50</b>	T50	M10	8.83	9,0	150	270	186	10	



### 2163 TXB

#### 3C-SCREWDRIVER for recessed TORX® head screws with pilot

- ✓ Blade in vanadium plus steel, chrome-plated
- ✓ 3-component handle with hanging hole
- ✓ TORX® = reg. trademark of Acument Intellectual Properties, LLC. USA




Code	No.	TXB	M	mm	mm	mm	mm	mm	mm	£
1828738	<b>2163 TXB T6</b>	T6	M2	1.69	3,0	60	140	29	10	
6677570	<b>2163 TXB T7</b>	T7	M2,5	1.99	3,0	60	140	25	10	
6677650	<b>2163 TXB T8</b>	T8	M2,5	2.31	3,0	60	140	29	10	
6677730	<b>2163 TXB T9</b>	T9	M3	2.50	3,0	60	140	29	10	
6677810	<b>2163 TXB T10</b>	T10	M3 - M3,5	2.74	3,0	80	160	30	10	
6678030	<b>2163 TXB T15</b>	T15	M3,5 - M4	3.27	3,5	80	170	45	10	
6678110	<b>2163 TXB T20</b>	T20	M4 - M5	3.86	4,0	100	190	51	10	
6678380	<b>2163 TXB T25</b>	T25	M4,5 - M5	4.43	4,5	100	200	68	10	
6678460	<b>2163 TXB T27</b>	T27	M4,5 - M6	4.99	5,5	115	215	84	10	
6678540	<b>2163 TXB T30</b>	T30	M6 - M7	5.52	6,0	115	225	105	10	
6678620	<b>2163 TXB T40</b>	T40	M7 - M8	6.65	7,0	130	240	125	10	

### 2163 BK

#### 3C-SCREWDRIVER for in-hex screws, with ball end

- ✓ Blade in vanadium plus steel, chrome-plated
- ✓ 3-component handle with hanging hole



Code	No.	BK	mm	mm	mm	mm	mm	mm	£
1828746	<b>2163 BK 2</b>	2	3	75	155	31	10		
6684430	<b>2163 BK 3</b>	3	4	75	155	36	10		
6684510	<b>2163 BK 4</b>	4	5	100	190	59	10		
6684780	<b>2163 BK 5</b>	5	6	100	200	86	10		
6684860	<b>2163 BK 6</b>	6	7	125	235	121	10		
6684940	<b>2163 BK 8</b>	8	10	150	270	210	10		
6685080	<b>2163 BK 10</b>	10	12	150	270	265	10		
6685160	<b>2163 BK 12</b>	12	14	160	280	349	10		

## 3C-SCREWDRIVER SETS

### 2150-2160 PH

#### 3C-SCREWDRIVER SET 6 pieces / 10 pieces

- ✓ Practical set composition in environmentally-friendly cardboard box
- ✓ For slotted and cross-slotted head screws PH
- ✓ Blades in vanadium plus steel, chrome-plated
- ✓ 3-component handle with hanging hole



2150-2160 PH-010

2150-2160 PH-06


Code	No.	Contents	mm	£
1482319	<b>2150-2160 PH-06</b>	⊖ 2150 4 5,5 6,5 8 ⊕ 2160 PH 1 2	660	1
1482343	<b>2150-2160 PH-010</b>	⊖ 2150 3 4 5,5 6,5 8 ⊖ 2153 5,5 ⊕ 2160 PH 1 2 ⊕ 2161 PH 1 ⊖ 4615 3,5	825	1



### 2154-2160 PH-07

#### 3C-SCREWDRIVER SET 7 pieces

- Practical set composition in environmentally-friendly cardboard box
- For slotted and cross-slotted head screws PH
- Blade with hexagon bolster
- Blade in vanadium plus steel, chrome-plated
- 3-component handle with hanging hole



Code	No.	Contents	📦	📅	£
1731149	2154-2160 PH-07	⊖ 2154 4,5 5,5 6,5 8 ⊕ 2160 PH 1 2 ⊖ 4615 3	715	1	

### 2150-2160 PZ-06

#### 3C-SCREWDRIVER SET 6 pieces

- Practical set composition in environmentally-friendly cardboard box
- For slotted and cross-slotted head screws PZ
- Blades in vanadium plus steel, chrome-plated
- 3-component handle with hanging hole




Code	No.	Contents	📦	📅	£
1482300	2150-2160 PZ-06	⊖ 2150 4 5,5 6,5 8 ⊕ 2160 PZ 1 2	670	1	

### 2160 PHZ-06

#### 3C-SCREWDRIVER SET 6 pieces

- Practical set composition in environmentally-friendly cardboard box
- For cross-slotted head screws PH and PZ
- Blade in vanadium plus steel, chrome-plated
- 3-component handle with hanging hole




Code	No.	Contents	📦	📅	£
2003589	2160 PHZ-06	⊕ 2160 PH 0 1 2 ⊕ 2160 PZ 0 1 2	344	1	


### 2163 BTX

#### 3C-SCREWDRIVER SET 5 pieces / 10 pieces

- Practical set composition in environmentally-friendly cardboard box
- For recessed TORX® head screws
- Blade in vanadium plus steel, chrome-plated
- 3-component handle with hanging hole
- TORX® = reg. trademark of Acument Intellectual Properties, LLC. USA



2163 BTX-05




2163 BTX-010

Code	No.	Contents	📦	📅	£
1482327	2163 BTX-05	⊕ 2163 BTX T10 T15 T20 T25 T30	435	1	
1482335	2163 BTX-010	⊕ 2163 BTX T7 T8 T9 T10 T15 T20 T25 T27 T30 T40	740	1	

### 2163 TXB-05

#### 3C-SCREWDRIVER SET 5 pieces

- Practical set composition in environmentally-friendly cardboard box
- For recessed TORX® head screws with pilot
- Blade in vanadium plus steel, chrome-plated
- 3-component handle with hanging hole
- TORX® = reg. trademark of Acument Intellectual Properties, LLC. USA



Code	No.	Contents	📦	📅	£
1616617	2163 TXB-05	⊕ 2163 TXB T10 T15 T20 T25 T30	440	1	

