

## Features

- 19" Device Compatibility
- Ventilation
- Suitable for 19" accessory installation.
- Cable entry options available.
- Optional cable entry at the back with plastic cover.
- Brush Cable Entry at the top.

## RS PRO Server Cabinets

RS Stock No.: 0749217



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

- *Areas of use: Offices (home, workplace), Branches (banks, government offices), Schools, Hospitals, Factories*
- *Purposes of use: Installation and setup of small systems, Intermediate distribution terminal, Floor distribution in network systems, Wall-mounted network installation applications*

## General Specifications

<b>Rack Units</b>	12U
<b>Type</b>	Wall Mount
<b>External Case Material</b>	Steel
<b>Base Material</b>	Metal
<b>Surface Finish</b>	Electrostatic Powder Coating
<b>Mounting</b>	Wall type
<b>Cabinet Size</b>	Width: 535.00mm Depth: 600.00mm
<b>Special Features</b>	Drop Sticker Logo
<b>Colour</b>	RAL9005
<b>Glass</b>	Tempered
<b>Ventilated</b>	Yes
<b>Fan Included</b>	No
<b>Adjustable Feet</b>	No
<b>EMC Shielding</b>	No

## Mechanical Specifications

<b>External Dimensions</b>	535.00mm x 600.00mm x 570.80mm
<b>External Height</b>	570.80mm
<b>External Width</b>	535.00mm
<b>External Depth</b>	600.00mm
<b>Internal Depth</b>	582.50mm
<b>Weight</b>	20.50kg

## Protection Category

IP Rating	IP20
-----------	------

## Approvals

Declarations	MFR Declaration of Conformity
Standards Met	CE Marking / 2014/30/EU / 2014/35/EU / 2011/65/EU (RoHS II) / EN 61587-1 / EN IEC 60297 Series / EN IEC 60917 Series / EIA/ECA-310-D/E / EN IEC 62262

## Similar Products

Stock No.	Brand	Colour	Material	Measurements
0749209	RS PRO	RAL9005	1mm Steel	H: 215.20mm D: 400.00mm
0749213	RS PRO	RAL9005	1mm Steel	H: 215.20mm D: 600.00mm
0749210	RS PRO	RAL9005	1mm Steel	H: 348.50mm D: 400.00mm
0749214	RS PRO	RAL9005	1mm Steel	H: 348.50mm D: 600.00mm
0749211	RS PRO	RAL9005	1mm Steel	H: 437.40mm D: 400.00mm
0749215	RS PRO	RAL9005	1mm Steel	H: 437.40mm D: 600.00mm
0749212	RS PRO	RAL9005	1mm Steel	H: 570.80mm D: 400.00mm

## Accessories

Stock No.	Brand	Colour	Material	Mounting location in the cabin
0749232	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749233	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749234	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749235	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749236	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749237	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749239	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749240	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
0749241	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails

<b>0749242</b>	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
<b>0749243</b>	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
<b>0749245</b>	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
<b>0749248</b>	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
<b>0749249</b>	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
<b>0749251</b>	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
<b>0749252</b>	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
<b>0749253</b>	RS PRO	RAL9005	1.0mm Steel	Top Chassis
<b>0749254</b>	RS PRO	RAL9005	1.0mm Steel	Top Chassis
<b>0749255</b>	RS PRO	RAL9005	1.0mm Steel	Top Chassis
<b>0749256</b>	RS PRO	RAL9005	1.0mm Steel	Top Chassis
<b>0749225</b>	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
<b>0749226</b>	RS PRO	RAL9005	1.2mm Steel	19" Device Mounting Rails
<b>0749246</b>	RS PRO	RAL9005	Steel	19" Device Mounting Rails
<b>0749247</b>	RS PRO	RAL9005	Steel	19" Device Mounting Rails

