



# Data sheet

## Foot Mounting Kits

RS Article Number	Description	Compatible Locknut Size
<a href="#">3043628</a>	Foot Mount Mini ISO 8-10mm	M12 x 1.25
<a href="#">3043634</a>	Foot Mount Mini ISO 12-16mm	M16x 1.5
<a href="#">3043640</a>	Foot Mount Mini ISO 20-25mm	M22 x 1.5

Locknuts are not supplied with the foot mounting kits.

The table below highlights which foot mount may be used with which cylinders:

Cylinder RS Part Number	Cylinder Description	Mounting Kit RS Part Number
3043448	Cylinder Mini ISO 10mm Bore 100mm Stk D/A	<a href="#">3043628</a>
3043397	Cylinder Mini ISO 10mm Bore 10mm Stk D/A	<a href="#">3043628</a>
3043274	Cylinder Mini ISO 10mm Bore 10mm Stk S/A	<a href="#">3043628</a>
3043404	Cylinder Mini ISO 10mm Bore 15mm Stk D/A	<a href="#">3043628</a>
3043410	Cylinder Mini ISO 10mm Bore 25mm Stk D/A	<a href="#">3043628</a>
3043353	Cylinder Mini ISO 10mm Bore 25mm Stk S/A	<a href="#">3043628</a>
3043426	Cylinder Mini ISO 10mm Bore 50mm Stk D/A	<a href="#">3043628</a>
3043280	Cylinder Mini ISO 10mm Bore 50mm Stk S/A	<a href="#">3043628</a>
3043432	Cylinder Mini ISO 10mm Bore 80mm Stk D/A	<a href="#">3043628</a>
3043454	Cylinder Mini ISO 12mm Bore 10mm Stk D/A	<a href="#">3043634</a>
3043785	Cylinder Mini ISO 12mm Bore 25mm Stk D/A	<a href="#">3043634</a>
3043779	Cylinder Mini ISO 12mm Bore 50mm Stk D/A	<a href="#">3043634</a>
3043533	Cylinder Mini ISO 16mm Bore 100mm Stk D/A	<a href="#">3043634</a>
3043763	Cylinder Mini ISO 16mm Bore 10mm Stk D/A	<a href="#">3043634</a>
3043476	Cylinder Mini ISO 16mm Bore 15mm Stk D/A	<a href="#">3043634</a>
3043814	Cylinder Mini ISO 16mm Bore 160mm Stk D/A	<a href="#">3043634</a>
3043820	Cylinder Mini ISO 16mm Bore 200mm Stk D/A	<a href="#">3043634</a>
3043482	Cylinder Mini ISO 16mm Bore 25mm Stk D/A	<a href="#">3043634</a>
3043375	Cylinder Mini ISO 16mm Bore 25mm Stk S/A	<a href="#">3043634</a>
3043498	Cylinder Mini ISO 16mm Bore 40mm Stk D/A	<a href="#">3043634</a>
3043505	Cylinder Mini ISO 16mm Bore 50mm Stk D/A	<a href="#">3043634</a>
3043381	Cylinder Mini ISO 16mm Bore 50mm Stk S/A	<a href="#">3043634</a>
3043511	Cylinder Mini ISO 16mm Bore 80mm Stk D/A	<a href="#">3043634</a>

Cylinder RS Part Number	Cylinder Description	Mounting Kit RS Part Number
3043577	Cylinder Mini ISO 20mm Bore 100mm Stk D/A	3043640
3043864	Cylinder Mini ISO 20mm Bore 125mm Stk D/A	3043640
3043858	Cylinder Mini ISO 20mm Bore 160mm Stk D/A	3043640
3043842	Cylinder Mini ISO 20mm Bore 200mm Stk D/A	3043640
3043836	Cylinder Mini ISO 20mm Bore 250mm Stk D/A	3043640
3043791	Cylinder Mini ISO 20mm Bore 25mm Stk D/A	3043640
3043319	Cylinder Mini ISO 20mm Bore 25mm Stk S/A	3043640
3043549	Cylinder Mini ISO 20mm Bore 40mm Stk D/A	3043640
3043555	Cylinder Mini ISO 20mm Bore 50mm Stk D/A	3043640
3043325	Cylinder Mini ISO 20mm Bore 50mm Stk S/A	3043640
3043561	Cylinder Mini ISO 20mm Bore 80mm Stk D/A	3043640
3043612	Cylinder Mini ISO 25mm Bore 100mm Stk D/A	3043640
3043921	Cylinder Mini ISO 25mm Bore 125mm Stk D/A	3043640
3043915	Cylinder Mini ISO 25mm Bore 160mm Stk D/A	3043640
3043909	Cylinder Mini ISO 25mm Bore 200mm Stk D/A	3043640
3043892	Cylinder Mini ISO 25mm Bore 250mm Stk D/A	3043640
3043583	Cylinder Mini ISO 25mm Bore 25mm Stk D/A	3043640
3043347	Cylinder Mini ISO 25mm Bore 25mm Stk S/A	3043640
3043886	Cylinder Mini ISO 25mm Bore 320mm Stk D/A	3043640
3043599	Cylinder Mini ISO 25mm Bore 40mm Stk D/A	3043640
3043870	Cylinder Mini ISO 25mm Bore 50mm Stk D/A	3043640
3043757	Cylinder Mini ISO 25mm Bore 50mm Stk S/A	3043640
3043606	Cylinder Mini ISO 25mm Bore 80mm Stk D/A	3043640

These cylinders are supplied with 1 x Piston Rod Locknut and 1 x Mounting Locknut.

This diagram shows where the lock nuts are supplied on the cylinders:

