

FEATURES

- Insulators for metric machine screws
- Provides electrical insulation
- Helps prevent electrolytic corrosion
- Can be used as lightly loaded bearings

RS PRO Nylon Screw Insulators

RS Stock No.:

2326874,2326848,2326927,2326928,2326929,
2326932,2326934,2326849,2326850,2326951,
2326851,2326852,2326853,2326971,2326854,2326974,
2326855,2326856,2326857,2326858,2326980,2327000,
2326861,2326862,2326863



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.


Nylon Screw Insulators

Product Description

Although primarily intended for the isolation of metal screws, these insulating spacers are also suitable for use as lightly loaded bearings.

Material Specifications

Material	Nylon 6,6
Colour	Natural



Note:

Dimensions referring to the line drawing:

Dimension **A** is Flange Diameter

Dimension **B** is Flange Thickness

Dimension **C** is Body Diameter

Dimension **D** is Hole Diameter/Inside Diameter

Dimension **E** is the Body Length

General Specifications

Stock No. [TR Reference]	To Suit Screw Size	A	B	C	D (Inside Dia)	E (Length)
2326874	M2	4.2	1	3	2.1	3
2326848	M3	6.2	1	4	3.1	2
2326927	M3	6.2	1	4	3.1	3
2326928	M3	6.2	1	4	3.1	4
2326929	M3	6.2	1	4	3.1	5
2326932	M3	6.2	1	4	3.1	6
2326934	M3	6.2	1	4	3.1	8
2326849	M4	8.2	1.5	6	4.1	3
2326850	M4	8.2	1.5	6	4.1	4
2326951	M4	8.2	1.5	6	4.1	5
2326851	M4	8.2	1.5	6	4.1	7
2326852	M4	8.2	1.5	6	4.1	9
2326853	M5	10.2	2	7	5.1	3
2326971	M5	10.2	2	7	5.1	4
2326854	M5	10.2	2	7	5.1	5
2326974	M5	10.2	2	7	5.1	7
2326855	M5	10.2	2	7	5.1	9
2326856	M6	12.2	2	8	6.1	4
2326857	M6	12.2	2	8	6.1	6
2326858	M6	12.2	2	8	6.1	8
2326980	M6	12.2	2	8	6.1	12
2327000	M8	14.2	2.5	10	8.1	4
2326861	M8	14.2	2.5	10	8.1	6
2326862	M8	14.2	2.5	10	8.1	8
2326863	M8	14.2	2.5	10	8.1	12

Nylon Screw Insulators

