

HC-D 50-SD-FQ/FS - Protective cover



1660193

<https://www.phoenixcontact.com/in/products/1660193>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective cover D50, for double locking latch, protective cover material: PA, height: 16.5 mm, seal: no, with lanyard

Commercial data

Item number	1660193
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF7
Product key	AF7AZC
Catalog page	Page 511 (C-4-2015)
GTIN	4017918021931
Weight per piece (including packing)	0.021 kg
Weight per piece (excluding packing)	0.021 kg
Customs tariff number	85389099
Country of origin	DE

HC-D 50-SD-FQ/FS - Protective cover



1660193

<https://www.phoenixcontact.com/in/products/1660193>

Technical data

Product properties

Product type	Protective cover
Housing type	Protective cover
Type	D50
Type	for supporting base element with double locking latch
Retaining cord present	yes
Seal present	no

Dimensions

Dimensional drawing	
Width	56 mm
Height	16.5 mm
Length	82 mm
Diameter	30 mm

Material specifications

Material Protective cover	PA
Flammability rating according to UL 94	HB
Material, protective cover	PA

Mechanical properties

Mechanical data

Locking type	Pin
--------------	-----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
Ambient temperature (operation)	-20 °C ... 100 °C

Mounting

Assembly note	Plastic protective cover for short-term protection
---------------	--

HC-D 50-SD-FQ/FS - Protective cover




1660193

<https://www.phoenixcontact.com/in/products/1660193>

Drawings

Dimensional drawing



Dimensional drawing

HC-D 50-SD-FQ/FS - Protective cover

1660193

<https://www.phoenixcontact.com/in/products/1660193>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1660193>



EAC

Approval ID: RU C-DE.AI30.B.01102

HC-D 50-SD-FQ/FS - Protective cover



1660193

<https://www.phoenixcontact.com/in/products/1660193>

Classifications

ECLASS

ECLASS-11.0	27440208
ECLASS-12.0	27440208
ECLASS-13.0	27440208

ETIM

ETIM 9.0	EC002314
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-D 50-SD-FQ/FS - Protective cover



1660193

<https://www.phoenixcontact.com/in/products/1660193>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in