

EMG755

Cut level E / A5 cut resistant glove with PU coating

A soft and comfortable high cut resistant glove with polyurethane coating. Ideal for handling sharp parts in dry or greasy conditions.

Features

- ▲ Cut resistance: Level E / A5
- ▲ A flexible and comfortable glove offering great dexterity
- ▲ Durable polyurethane palm coating ensures good protection against abrasion
- ▲ Contact heat protection up to 100°C / 212°F for a short period (15 sec max)
- ▲ Reinforced thumb crotch enhances durability
- ▲ Designed for easy movement and continuous wear
- ▲ Breathable back of hand to reduce perspiration
- ▲ Seamless knit prevents irritation

Certifications



Suitable industries & applications

Industries

- ▲ Aerospace
- ▲ Automotive

- ▲ Construction

Applications

- ▲ Component and Product Assembly
- ▲ General Goods Handling
- ▲ Woodwork and Fabrication
- ▲ General Maintenance



Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

EMG755

Cut level E / A5 cut resistant glove with PU coating

Product information

Materials	Liner:	13 Gauge HPPE, Nylon, Steel Fibre
	Coating:	Polyurethane
Colour	Grey / Black	
Length	220mm	
Cuff Style	Elasticated Knit Wrist	

Ordering information

XS	EMG00755FB	Items per Pack 10 x Pairs
S	EMG00755FD	
M	EMG00755FF	Items per Case 120 x Pairs
L	EMG00755FH	
XL	EMG00755FJ	
XXL	EMG00755FL	
XXXL	EMG00755FN	

Additional information

Certification legend



or click [here](#)

Declaration of conformity



or click [here](#)

View product online



or click [here](#)

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM
Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES
Globus Americas LLC, 45 Rockefeller Plaza, Suite 2000, New York City, New York, 10111, USA

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment.
The manufacturer reserves the right to make any modifications it deems necessary.