



## SERIES S1 IMPACT WRENCH 3/4"

### RC3780

#### SAM Outillage

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:47





## DESCRIPTION

### SERIES S1 IMPACT WRENCH 3/4"

**PRACTICAL:** Tightening / loosening reversal with one pushbutton, 3 tightening speeds and 1 loosening speed.  
**COMFORT:** Two-material handle for greater comfort.  
**POWERFUL:** Exceptional weight/power ratio.

Compact wrench for intensive use for industrial and automotive maintenance jobs. Wrench covering all 3/4" applications. Double hammer punch, low vibrations, low consumption. Three-position torque variator and control button on the front. Suspension ring.

#### HIGH-PERFORMANCE

It has an exceptional weight/power ratio (40% better than our main competitors).

It easily performs common and repetitive operations, and delivers its full power when loosening. Its optimised impact system delivers the required jolt-free power.

#### COMPLETE

The 1163 has the components expected by the market - 3-position regulator, ergonomic handle, two-material casing, good

#### SAM Outillage

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:47



weight/power ratio, low consumption...

**ECONOMICAL**

Compact, lightweight impact wrench (2.6 kg) - currently the lightest on the market in its category. It allows the user to perform all operations with just one hand, while wearing gloves.

Wrench covering every possible 3/4" application. Its double-hammer offset impact system is suitable for all types of tightening operation, even for low-torque applications. It has energy-consumption levels nearly 40% lower than standard 3/4" wrenches. This wrench coupled with the flexible multi-flow accessory (Ref. 19015-MF) regulates the flow to 200 or 400 l/mn. It saves compressor power and can generate air consumption savings of up to 60%. Suspension ring.

**SPECIFIC DATA**

Designation	IMPACT WRENCH 3/4"
Sales reference	RC3780
L (mm)	191
Weight (g)	2950
Rotation speed (rpm)	5000
Vibration (m/s <sup>2</sup> )	8,5
Noise level (dBa)	90
C mm	6,5
C min mm	
C mm	1/4
Maximum input torque Nm	1492
Hammer type	
Guarantee	M2   SAM Equipment and Machine Guarantee

**SAM Outillage**

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>



**Guarantee applied**

**M2 | SAM Equipment and Machine Guarantee**

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

[>> Find out more](#)

**SAM Outillage**

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:47

