

# Product data sheet

Specifications



plug-in solid state relay- 12.5 mm -  
input - 24 V DC type 2

ABS7EC3B2

Product availability: Stock - Normally stocked in distribution facility

## Main

Range of Product	Advantys Telefast ABE7
Product or Component Type	Plug-in solid state relay
Relay Type	Input relay
minimum ordered quantity	Set of 4

## Complementary

Response time	<= 0.05 ms from state 0 to 1 <= 0.4 ms from state 1 to 0
Width pitch dimension	0.5 in (12 mm)
Product Compatibility	ABE7P16F310 ABE7P16F310E ABE7P16F312
Discrete input voltage	24 V DC, type 2
Discrete output voltage	5...24 V DC
Net Weight	0.031 lb(US) (0.014 kg)

## Ordering and shipping details

Category	US10CP222375
Discount Schedule	0CP2
GTIN	3389110720808
Returnability	Yes
Country of origin	LV

## Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	1.97 in (5.000 cm)
Package 1 Width	2.05 in (5.200 cm)
Package 1 Length	2.56 in (6.500 cm)
Package weight(Lbs)	0.388 oz (11.000 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Height	1.97 in (5.000 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	2.05 in (5.200 cm)
Package 2 Length	2.56 in (6.500 cm)
Package 2 Weight	1.623 oz (46.000 g)
Unit Type of Package 3	S02
Number of Units in Package 3	128
Package 3 Height	5.91 in (15.000 cm)
Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	4.085 lb(US) (1.853 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)


[How we assess product sustainability >](#)

Environmental footprint	
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	<a href="#">REACH Declaration</a>
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
PVC free	Yes

Use Again

Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Connections and Schema

Internal Wiring Diagram

---




Image of product / Alternate images

Alternative

---

