

Features

- Auto standby
- Auto sleep
- Temperature lock
- °C / °F switch
- LED display
- Universal soldering tip

RS PRO Soldering Station 70W, 230V, 50-500°C

RS Stock No.: 0631069



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range

has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RRS PRO Digital Soldering Station

This digital soldering station comes with a heavy-duty soldering iron with a ceramic heating element. By equipping a digital temperature control unit, it enables users to precisely understand what temperature he is soldering, which is a great option for projects where requires temperature limitation. Moreover, with 70W PCT heating element, it could quickly soar to defaulted 350°C soldering temperature. Yet it could save your energy as it could wake up or sleep automatically by detecting users' operation with ergonomic-design handle. Wide temperature range of 50-500°C (122-932° F) could meet all your project soldering needs.

Features and Benefits

- Universal series lead-free long life iron tip, convenient to change tips..
- LED display for easy and clear menu operation, ° C / ° F conversion, auto standby & sleep function, etc..
- Built-in PID system to ensure high stability, excellent performance and precise accuracy.

General Specifications

Plug Type	Type G – British 3-pin; Type E (France-2 round pins + hole for ground)
Tasks Supported	Soldering
Wattage	70 W
Input Voltage	230 V
Soldering Tip Temperature	50-500 °C
Number of Outputs	2

Display Type	LED
ESD Safe	No

Approvals

Declarations	REACH DoC
Standards Met	CE, UKCA, RoHS

Similar Products

Stock No.	Brand	Product Name	Wattage	Tasks Support	Plug Type
0631067	RS PRO	Soldering Station	60W	Desoldering / Soldering	Type G & Type E
0631068	RS PRO	Soldering Station	80W	Desoldering / Soldering	Type G & Type E
0631069	RS PRO	Soldering Station	70W	Desoldering / Soldering	Type G & Type E
0631071	RS PRO	Soldering Station	80W	Desoldering / Soldering	Type G & Type E
0631072	RS PRO	Soldering Station	60W	Desoldering / Soldering	Type G & Type E
0631066	RS PRO	Soldering Iron	90W	Desoldering / Soldering	Type G & Type E

Soldering Iron

Stock No.	Brand	Product Name	Power Type	Wattage	Voltage	Temperature Range
0631079	RS PRO	Soldering Iron	Electric	70W	AC 25V (MAX)	50-500 °C


Soldering Tips

Stock No.	Brand	Tip Shape	Tip Size	Tip Angle
2024516	RS PRO	Straight Chisel	1.6 mm	0°
2024517	RS PRO	Straight Hoof	0.5 mm	45°
2024518	RS PRO	Straight Hoof	0.8 mm	45°
2024520	RS PRO	Straight Hoof	1 mm	60°
2024521	RS PRO	Straight Conical	0.2 mm	0°
2024522	RS PRO	Straight Conical	0.2 mm	0°
2024523	RS PRO	Straight Conical	0.5 mm	0°
2024524	RS PRO	Straight Knife	2 mm	45°
2024526	RS PRO	Straight Knife	1.6 mm	45°
2024527	RS PRO	Straight Conical	0.2 mm	0°
2024528	RS PRO	Straight Hoof	3 mm	45°
Stock No.	Brand	Tip Shape	Tip Size	Tip Angle
2024529	RS PRO	Straight Hoof	4 mm	45°
2024530	RS PRO	Bent Conical	0.2 mm	153°
2024532	RS PRO	Straight Knife	2 mm	45°
2024533	RS PRO	Bent Conical	0.5 mm	153°
7998973	RS PRO	Conical Chisel	2.4 mm	
7998976	RS PRO	Conical Sharp	0.2 mm	
7998979	RS PRO	Conical Chisel	1.2 mm	
7998982	RS PRO	Conical Chisel	3.2 mm	
7998985	RS PRO	Straight Conical	0.8 mm	
7998989	RS PRO	Conical Bevel	2 mm	45°

Accessory

Stock No.	Brand	Product Name	Material	For Use With
-----------	-------	--------------	----------	--------------


136-8299	RS PRO	Solder Tip Cleaner kit	Plastic holder with brass wool	Gentle Fine Clean of Soldering Tip
136-8300	RS PRO	Brass Wool for solder Tip Clean	Brass Wool	Gentle Fine Clean of Soldering Tip (1368299, 0631071, 0631069, 0631068)
0631073	RS PRO	Soldering Iron Cleaning Sponge (PK of 5)	N/A	0631068, 0631067, 0631072



Main unit



Soldering Iron



Iron stand



Brass wool